

Brand Name: Acer
DVI: Yes
Environmentally Friendly: Yes
Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
Number of USB 2.0 Ports: 4
Number of USB 3.0 Ports: 4
Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 10 Pro
Optical Drive Type: DVD-Writer
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3
Product Family: Veriton X2640G
Product Type: Desktop Computer
Standard Memory: 4 GB
Total Hard Drive Capacity: 1 TB
Total Number of USB Ports: 8
VGA: Yes

Display & Graphics

Graphics Controller: Intel
Manufacturer:
Graphics Controller Model: HD Graphics 530
Graphics Memory Accessibility: Shared
Graphics Memory Technology: DDR4 SDRAM
TV Card: No

General Information

Brand Name: Acer
Manufacturer Part Number: DT.VMXEK.020
Manufacturer Website Address: <http://www.acer.co.uk>
Manufacturer: Acer, Inc
Product Line: Veriton
Product Name: Veriton X2640G Desktop Computer
Product Series: X2640G
Product Type: Desktop Computer

I/O Expansions

Number of PCI Express x1 Slots: 1
Number of PCI Express x16 Slots: 1
Number of Total Expansion Slots: 2

Input Devices

Keyboard Type: Physical Keyboard
Keyboard: Yes
Pointing Device Type: Mouse

Interfaces/Ports

Audio Line In: Yes
Audio Line Out: Yes
DVI: Yes
Modem (RJ-11): No
Network (RJ-45): Yes
Number of USB 2.0 Ports: 4
Number of USB 3.0 Ports: 4
Number of USB 3.1 Gen 1 Ports: 4
Total Number of USB Ports: 8
VGA: Yes

Memory

Maximum Memory: 16 GB
Memory Card Reader: Yes
Memory Card Supported: SD
Memory Standard: DDR4-2133/PC4-17000
Memory Technology: DDR4 SDRAM

Standard Memory: 4 GB

Miscellaneous

Certifications & Standards:

- DMI
- GS
- PC2001
- Citrix ready
- BSMI
- VCCI
- CE
- FCC
- CB

Environmental Certification: RoHS

Environmentally Friendly: Yes

Features: Security Slot

Package Contents:

- Veriton X2640G Desktop Computer
- USB Keyboard
- USB Mouse

Network & Communication

Ethernet Technology: Gigabit Ethernet

Modem: No

Physical Characteristics

Depth: 354 mm

Height: 265 mm

Width: 100 mm

Power Description

Maximum Power Supply Wattage: 220 W

Processor & Chipset

64-bit Processing: Yes

Cache: 3 MB

Chipset Manufacturer: Intel

Chipset Model: H110 Express

Direct Media Interface: 8 GT/s

Hyper-Threading: Yes

Number of Processors Installed: 1

Number of Processors Supported: 1

Processor Core: Dual-core (2 Core)

Processor Manufacturer: Intel

Processor Model: i3-6100

Processor Speed: 3.70 GHz

Processor Type: Core i3

vPro Technology: No

Software

Operating System Architecture: 64-bit

Operating System Platform: Windows

Operating System: Windows 10 Pro

Software Included: Microsoft Office trial

Storage

Hard Drive Configuration: 1 x 1 TB

Hard Drive Interface: Serial ATA/300

Hard Drive RPM: 7200

Number of Hard Drives: 1

Optical Drive Type: DVD-Writer

Optical Media Supported: DVD-RAM/±R/±RW

Total Hard Drive Capacity: 1 TB