

Brand Name: Acer
DVI: Yes
Environmentally Friendly: Yes
Number of USB 2.0 Ports: 4
Number of USB 3.0 Ports: 4
Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 7 Professional
Optical Drive Type: DVD-Writer
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3
Product Family: Veriton X2640G
Product Type: Desktop Computer
Standard Memory: 4 GB
Total Number of USB Ports: 8
Total Solid State Drive Capacity: 128 GB
VGA: Yes

Display & Graphics

TV Card: No

General Information

Brand Name: Acer
Manufacturer Part Number: DT.VMXEK.018
Manufacturer Website Address: <http://www.acer.co.uk>
Manufacturer: Acer, Inc
Product Line: Veriton
Product Name: Veriton X2640G Desktop Computer
Product Series: X2640G
Product Type: Desktop Computer

I/O Expansions

Number of PCI Express x1 Slots: 1
Number of PCI Express x16 Slots: 1
Number of Total Expansion Slots: 2

Input Devices

Keyboard Type: Physical Keyboard
Keyboard: Yes
Pointing Device Type: Mouse

Interfaces/Ports

Audio Line In: Yes
Audio Line Out: Yes
DVI: Yes
Modem (RJ-11): No
Network (RJ-45): Yes
Number of USB 2.0 Ports: 4
Number of USB 3.0 Ports: 4
Number of USB 3.1 Gen 1 Ports: 4
Total Number of USB Ports: 8
VGA: Yes

Memory

Maximum Memory: 16 GB
Memory Card Reader: Yes
Memory Card Supported: SD
Memory Standard: DDR4-2133/PC4-17000
Memory Technology: DDR4 SDRAM
Standard Memory: 4 GB

Miscellaneous

Certifications & Standards:

- DMI
- GS
- PC2001
- Citrix ready
- BSMI
- VCCI
- CE

Environmental Certification:

- FCC
- CB

RoHS
Environmentally Friendly: Yes
Features: Security Slot
Package Contents:

- Veriton X2640G Desktop Computer
- USB Keyboard
- USB Mouse

Network & Communication

Ethernet Technology: Gigabit Ethernet
Modem: No

Physical Characteristics

Depth: 354 mm
Height: 265 mm
Width: 100 mm

Power Description

Maximum Power Supply Wattage: 220 W

Processor & Chipset

64-bit Processing: Yes
Cache: 3 MB
Chipset Manufacturer: Intel
Chipset Model: H110 Express
Direct Media Interface: 8 GT/s
Hyper-Threading: Yes
Number of Processors Installed: 1
Number of Processors Supported: 1
Processor Core: Dual-core (2 Core)
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3
vPro Technology: No

Software

Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 7 Professional
Software Included: Microsoft Office trial

Storage

Number of Solid State Drives: 1
Optical Drive Type: DVD-Writer
Optical Media Supported: DVD-RAM/±R/±RW
Solid State Drive Configuration: 1 x 128 GB
Solid State Drive Interface: Serial ATA/300
Total Solid State Drive Capacity: 128 GB