

## Rack Mount Intake Blowers *HB Series*

### Features



- Standard 19" rack mount
- Air delivery from more than 50% of their 17" width
- Internal neoprene isolation mounts reduce transmission of vibration to the rack
- Air intake only, to pressurize the rack with filtered air
- Heavy steel construction
- Attractive 19" stainless steel grille included
- 115 VAC, 50/60 Hz. motor is UL recognized, CSA certified, ball bearing type cooled by incoming air
- Includes permanent filter (replacement filters available below)
- Comes with 6' STJ 3- wire cord
- Optional replacement filters come in a pack of five (5).

### Accessories

- Filter Coat
- Mounting Hardware

Part No.	Free Flow Air Delivery (CFM)	Running Amps	RPM Nominal	Noise (dB)	Blower Type	Ambient Temperature (F)	Mounting Dimensions Rack Units	Height (in)	Recessed
<b>HB2160A</b>	145 / 125	0.7	2500 / 3000	62	TransverseFlow	-20 to +250	2U	3.50	<b>H</b>
<b>HB3250A</b>	155 / 200	1.2	2750 / 3000	72	Double Centrifugal	-20 to +250	3U	5.25	<b>H</b>
<b>HB4500A</b>	405 / 465	2.5	2750 / 3300	76	Double Centrifugal	-20 to +250	4U	7.00	<b>H</b>

*Data subject to change without notice*