

Lite Duty Caster Set *1425P Series*



Features

- Twin nylon swivel wheels with zinc axles and hoods.
- 5/16 - 18 threaded stem mounts into existing holes in base of rack (in place of leveling feet).
- Final mounting height of 2.75" (70 mm).
- Features zinc plated ball bearing pivot, composite wheels.

Compatibility

- RCHS/RCHV
- RCSC
- REFK
- DNRRHDW
- RS
- 1564

Part No.	Strength	Wheel Diameter	Overall Height		Caster Set Weight Capacity	Quantity Included In Set	Brakes Included	Physical Wheel Weight
			Added to Cabinet	to Cabinet				
1425P	Lite Duty	2.37	2.75		400	4	No	3 lb (1.4 kg)

Data subject to change without notice