

Two Post Mounting Adjustable Shelf *DNRMA Series*

Features



- 14 Gauge steel construction.
- Movable side brackets allow mounting inside or outside rack at 4 different depths
- Designed mainly for open relay racks - works panel mounted on any rack
- Choice of 16" or 20" deep
- Available in either 19" or 23" rack panel width
- Finished in rugged textured - black powder paint
- Knockdown design ships unassembled for easy handling and shipping protection.
- Tested to nearly double the suggested load rating of 275 lbs.
- RoHS and REACH compliant.
- Manufactured in North America.

Accessories

- Mounting Hardware

Part No. 19 Inch Mounting	Part No. 23 Inch Mounting	Overall Depth	Mounting Dimensions	
			Rack Units	Height
DNRMA1916BK1	DNRMA2316BK1	16.00	3U	5.25
DNRMA1920BK1	DNRMA2320BK1	20.00	3U	5.25

Data subject to change without notice