


# Adjustable Depth 4-Post Rack Mount Shelf *RMAS Series*

## Features



- Adjustable mounting depth.
- Choice of vented or solid options.
- Constructed of 14-Gauge Steel.
- Finished in a rugged textured powder paint finish
- Includes all mounting hardware
- MOUNTS ON TWO PAIR OF PANEL RAILS (FRONT & BACK)
- RoHS and REACH compliant.
- Manufactured in North America.

**For heavy duty, full-depth shelving requirements, check out our new ADS Series.**



## Accessories

- Mounting Hardware



## Light Duty Shelves

Part No. Solid	Part No. Vented	Overall Shelf Depth	Adjustable Depth Range		Rack Units
			Min	Max	
RMASU1917BK1	RMASV1917BK1	17.00	17.00	27.00	1U
RMASU1925BK1	RMASV1925BK1	25.00	25.00	35.00	1U
RMASU1930BK1	RMASV1930BK1	30.00	30.00	40.00	1U

Suggested Load Capacity of 75 lbs

## Heavy Duty Shelves

Part No. Solid	Part No. Vented	Overall Shelf Depth	Adjustable Depth Range		Rack Units
			Min	Max	
RMASUHD1917BK1	RMASVHD1917BK1	17.00	17.00	27.00	2U
RMASUHD1925BK1	RMASVHD1925BK1	25.00	25.00	35.00	2U
RMASUHD1936BK1	RMASVHD1936BK1	36.00	36.00	48.00	2U

Suggested Load Capacity of 200 lbs

*Data subject to change without notice*

