

## Small Head 10-32 Thumb Screw *1421TS Series*

### Features



- 10-32 x 0.625 inch length steel thumb screws.
- Slotted & Phillips combination pan head screws.
- Black oxide finish.
- Includes integral - factory installed, mar resistant nylon washer.
- Saves installation time & panel space (required when mounting multiple 1U (1.75") panels or 1U equipment close spaced).
- Packaged in a reusable jar.



Part No.	Qty Included	Screw Head Diameter	Screw Head Height	Screw Length
<b>1421TS100BK</b>	100 screws with nylon washers	0.45	0.38	1.00
<b>1421TS250BK</b>	250 screws with nylon washers	0.45	0.38	1.00

*Data subject to change without notice*