

## Economy Swing-Out Wall Mount Cabinet *SWCC Series*

**Note:** This product line has been discontinued as a stocked series. Information is for reference only. It has been replaced with **RB-SW Series**. For alternative solution assistance, please contact Hammond Customer Service - [sales@hammfg.com](mailto:sales@hammfg.com) or USA (716) 630-7030, Canada and International (519) 822-2960.



### Features

- Double-hinged for easy rear access (body swings open to 120°).
- Constructed in light duty 16-gauge steel.
- Includes two (2) pairs of EIA-310-D compliant square hole punched rails with 19" mounting.
  - Starter pack of M5 screws and cage nuts included.
  - For 10-32 hardware see the **CAGKIT Series**.
- Rails are adjustable in depth in 25mm increments.
- Tempered glass front door opens a full 180°.
- Front and sides vented for air flow.
- Removable side panels can be locked using optional key lock **SWCCLOC**.
- Rear cable access.
- Provision for optional fans on top panel.
- Ships assembled - ready to install.
- Finished in smooth black powder paint.
- Tested to nearly double the suggested load rating of 80 lbs.
- RoHS Compliant.

**RACK BASICS®**



Part No.	Overall Dimensions			Mounting Dimensions			Usable Rack		Replaced by Part No.
	Height	Width	Depth	Height	Width	Depth	Depth	Units	
<b>SWCC1901021BK2</b>	14.18	23.70	21.80	10.50	19.00	10.98	20.91	6U	<b>RB-SW9</b>
<b>SWCC1901521BK2</b>	20.40	23.70	21.80	15.75	19.00	10.98	20.91	9U	<b>RB-SW9</b>
<b>SWCC1902121BK2</b>	25.60	23.70	21.80	21.00	19.00	10.98	20.91	12U	<b>RB-SW12</b>
<b>SWCC1902621BK2</b>	30.90	23.70	21.80	26.25	19.00	10.98	20.91	15U	<b>RB-SW15</b>
<b>SWCC1903121BK2</b>	36.10	23.70	21.80	31.50	19.00	10.98	20.91	18U	<b>RB-SW18</b>

Usable depth refers to the spacing between the inside of glass door to the inner rear of the enclosure.

### Lock for Side Panels

Part No.	<b>SWCCLOC</b>
----------	----------------

*Data subject to change without notice*

