


## Class 2 Energy Limiting Box Mount *BF Series*



### Features

- Used in chimes, door bells, security systems, decorative lighting, furnaces, humidifiers, appliances, vending machines, intercom system type applications.
- Rugged, low noise design, indoor use only.
- Stripped wire input (primary) leads, screw terminal output (secondary).
- Mounted on box plate for easy installation.
- Input leads are black 6" minimum, on 240V models 240V lead is red.
- All models are designed for 50/60 Hz. operation - limited by built in circuit breaker.
- c UL us listed #E184371 - Class 2 Not inherently limited
- CSA certified (209651)



Part No.	A.C. Input (Primary)	A.C. Output Secondary (RMS)		Power Rating	Overall Dimensions		
	V (RMS)	V	A	VA	A	B	C
<b>BF2F</b>	120	16	4.68	75	3.00	2.50	3.75
<b>BF5F</b>	240	16	4.68	75	3.00	2.50	3.75
<b>BF2G</b>	120	24	3.13	75	3.00	2.50	3.75
<b>BF5G</b>	240	24	3.13	75	3.00	2.50	3.75



*Data subject to change without notice*