


24V / Small Control Open Style, Chassis Mount *PHC*

Series






120V, 208V, 347V or 600V Primary



Features

- Used as a small 24 volt transformer for relay, pilot lights or low voltage, low power control use.
- 60 Hz. operation.
- Chassis mount.
- With 10" leads.
- CSA certified (209651)
- UL listed (File #E50394)

Gallery



Part No.	Primary Voltage	Secondary Voltage	Secondary		Overall Dimensions			Mounting
			Current (Amps)	VA	Height (C)	Width (A)	Depth (B)	Hole Centers (D)
PHC50PGA	24	24 VCT	2.08	50	2.63	4.00	2.25	3.56
PHC25JGA	120	24	1.04	25	2.31	3.69	2.13	3.13
PHC50JGA	120	24	2.08	50	2.63	4.00	2.50	3.56
PHC25LGA	208	24	1.04	25	2.31	3.69	2.13	3.13
PHC50LGA	208	24	2.08	50	2.63	4.00	2.50	3.56
PHC25KGA	347	24	1.04	25	2.31	3.69	2.13	3.13
PHC50KGA	347	24	2.08	50	2.63	4.00	2.50	3.56
PHC25FGA	480	24	1.04	25	2.31	3.69	2.13	3.13
PHC50FGA	480	24	2.08	50	2.63	4.00	2.50	3.56
PHC25AGA	600	24	1.04	25	2.31	3.69	2.13	3.13
PHC50AGA	600	24	2.08	50	2.63	4.00	2.50	3.56

Data subject to change without notice

