

125-1300 W Fan Heater with Thermostat *FLH Series*



Features

- Designed to prevent condensation or maintain minimum temperature in enclosures.
- Built in Thermostat. (-18 C to +38 C) (0 F to +100 F)
- Fan Auto/On switch with pilot light for Heat On indication
- High temperature safety protection
- Aluminum alloy outer casing
- Connection via terminal block.
- 1300W models are cURus approved only.

Part No.	Watts	Voltage	Hz	CFM	Overall Dimensions		Ship Wt.
					Height x Width x Depth	lbs	
FLHTF125A115	125 W	120 V	60	20	5.5" x 4.0" x 5.3"		2.2
FLHTF125A230	105/125 W	220/240 V	50/60	20	5.5" x 4.0" x 5.3"		2.2
FLHTF200A115	200 W	120 V	60	20	5.5" x 4.0" x 5.3"		2.2
FLHTF200A230	165/200 W	220/240 V	50/60	20	5.5" x 4.0" x 5.3"		2.2
FLHTF400A115	400 W	120 V	60	20	7.5" x 4.0" x 5.3"		3
FLHTF400A230	335/400 W	220/240 V	50/60	20	7.5" x 4.0" x 5.3"		3
FLHTF800A115	800 W	120 V	60	20	7.5" x 4.0" x 5.3"		3
FLHTF800A230	670/800 W	220/240 V	50/60	20	7.5" x 4.0" x 5.3"		3
FLHTF1300A115	1300 W	120 V	60	50	7.5" x 5.6" x 6.9"		4
FLHTF1300A230	1080/1300 W	220/240 V	50/60	50	7.5" x 5.6" x 6.9"		4

Data subject to change without notice