

250-400 W Fan Heater *SHGL Series*



Features

- For use when larger heating capacities or internal forced air circulation is required.
- Designed to prevent condensation or maintain minimum temperature in enclosures.
- Thermostats are also available.

Accessories

- Temperature Controls

Part No.	Watts	Surface Temperature	Starting Current	Dimensions	
				Length x Width x Depth	Ship Wt. lbs
SHGL04600	250	167°F	2.2 A	7.00 x 3.15 x 3.15	2
SHGL04601	400	167°F	3.5 A	9.76 x 3.15 x 3.15	3

Operating Voltage:	AC 110-120 V, 50/60 Hz
Circulation Power:	20 CFM Free Blowing
Axial Fan:	Ball Bearing
Durability:	30,000 hrs. at 68°F ambient temperature
Heating Element:	Resistance heating element with temperature limiter
Heating Body:	Extruded aluminum, black anodized
Connection:	3 pole terminal for 12 AWG
Mounting:	Easily installed by clip mounting on 35 mm DIN rails (included)
Protection Class:	1 (tested for grounding at 1250 V)
Protection:	IP20
Approval:	UL Recognized Component, cUL Recognized Component, CE

Data subject to change without notice