

Deep Channel Knockdown Steel 2-Post Rack *DNRRDCK*

Series

1,200 lbs Weight Capacity

X **Note:** This product line has been discontinued as a stocked series. Information is for reference only. For alternative solution assistance, please contact Hammond Customer Service - sales@hammfg.com or USA (716) 630-7030, Canada and International (519) 822-2960.



Features

- Constructed in 12-gauge steel (base) and 14-gauge steel (rails).
- EIA-310-D compliant 10-32 front and rear tapped (8" deep) rails with 19" mounting.
- Includes large base for freestanding support of equipment.
- Finished in smooth black powder paint.
- Knockdown design ships unassembled for easy handling and shipping protection.
- Tested to nearly double the suggested load rating of 1,200 lbs (544 kg).
- RoHS Compliant.
- Manufactured in North America.

Accessories

- Universal Rack Shelf
- Two Post Mounting Clamping Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- Outlet Strips
- 10-32 Mounting Hardware
- Grounding
- Rack Unit Label
- Two Post Mounting Adjustable Shelf
- Two Post Mounting Deep Channel Battery Shelf
- Adjustable Depth DIN Rail Panel
- Hinged Acrylic Door Panel Cover
- Cable Management
- Rack Panels
- Rack and Cabinet Baying/Ganging/Joining Kit

Part No.	Overall Dimensions			Mounting Dimensions		
	Height	Width	Depth	Height	Width	Rack Units
DNRR1942DCK	45.13	20.88	26.00	42.00	19.00	24U
DNRR1970DCK	73.13	20.88	26.00	70.00	19.00	40U
DNRR1977DCK	80.13	20.88	26.00	77.00	19.00	44U

