

blupont™



Model	DVR-4CH-A72-BP
System	
Operating System	Embedded LINUX
Video	
Multi-mode input	Analog: 4*1080N, 4*720P, 4*960H; Mixing: 2*AHD-M (analog) + 2*720P(network); Network: 8*1080P; 12*960P; 8*720P; 4*1080P; 4*720P; 1*1080P
Input	4CH BNC
Signal Type	AHD/CVI/TVI2.0/Analog/Network
Output	1CH Out/ VGA ,1CH Out/HDM (Support:1920*1080P)
Audio	
Input	4Channel, RCA
Two-way Audio	NO
Output	1 Channel, RCA
Alarm	
Sensor Input	NO
Output	NO
Motion Detection	16 × 12 grids per channel;6 adjustable parameters for accurate detection(for local analog channel only)
Trigger Events	Recording, PTZ, Tour, Email
Email Alarm	Send Strings to The Designated E-mail
PTZ	
Interface	RS485
Protocol	Support more than 20 kinds protocols.
Baud Rate	1200~115200
Address	1~255
Display	
VGA	Resolution:1920*1080,1280*720,1440*900,1280*1024,1024*768
HDMI	Resolution:1920*1080,1280*720,1440*900,1280*1024,1024*768
Display Split	1/4/8/9 screen
Privacy Masking	4 Rectangular Zones (local camera)
OSD	Camera title, Time, Video loss, Alarm, Motion detection, Recording
Recording	
Video Compression	H.264
Audio Compression	G.711A
Resolution	1080P/720P/960H
Video Quality	Best/Better/Good/General/worse/worst
Record Rate	1080N(960*1080 4*25fps),720P(1280*720 4*25fps), 960H(P:960*576 4*25fps/N:960*480 4*30fps)
Record Mode	Manual\Timer\Motion Detection
Playback & Backup	
Sync Playback	4 Channel(All HD Analog Mode)/ 1Channel
Remote Playback	4 Channel/1channel
Search Mode	ALL, Channel, Manual, Time, Date, Motion Detection
Playback Functions	Play, Pause, Stop, Rewind, Fast Play, Slow Play, Digital zoom
Backup Mode	USB Device/Network
Network	
Interface	1*RJ45 10/100 Base-T self-adaptive Ethernet port
Network Functions	DHCP、PPPOE、NTP、Email、IP Authority、DDNS、FTP、ARSP、Alarm Center、Wireless Dialing、Mobile Monitor、UPNP、Wifi、RTSP、Cloud Service
DDNS	3322、dyndns、oray、myq-see,etc
Web Browser	Internet Explorer
CMS Software	Support Windows XP /Windows Vista/Windows 7

Extra Stream	D1/CIF/QCIF(1~25fps)
Smart Phone	iPhone, Andriod
Hard Disk Driver	
Interface Type	1 SATA Interface
Capacity	Up to 6TB Capacity
General	
Language	Support 27 languages (SimChinese、TradChinese、English、Farsi、Finnish、French、German、Greek、Hungarian、Italian、Japanese、Poland、Portugal、Russian、Spanish、Thai、Turkey 、Vietnamese、Romanian、Brazilian、korean、Indonesian、Swedish、Arabic、Bulgarian、Czech、Hebrew)
USB Interface	2 USB 2.0 Interfaces , supporting USB mouse
Power Supply	DC12V/2A
Working Environment	0°C ~ +55°C/10~90%
Dimension (W×D×H)	260*190*43(mm)
Weight	2kg