

blupont™



Model	DVR-16CH-A72-BP
System	
Operating System	Embedded LINUX
Video	
Multi-mode input	Anolog: 16*1080N; 8*1080N; Anolog+Network: 8*1080N(Anolog)+8*960P(Network); Network:8*1080P+8*960P; 16*960P; 4*3M; 4*5M;
Input	16CH BNC
Signal Type	AHD/CVI/TVI2.0/Anolog/Network
Output	1CH Out/ VGA ,1CH Out/HDMI (Suport:1920*1080P)
Audio	
Input	2Channel
Two-way Audio	NO
Output	1 Channel, RCA
Alarm	
Sensor Input	NO
Output	NO
Motion Detection	16 × 12 grids per channel;6 adjustable parameters for accurate detection(for local analog channel only)
Trigger Events	Recording, PTZ, Tour, Email
Email Alarm	Send Strings to The Designated E-mail
PTZ	
Interface	RS485
Protocol	Support more than 20 kinds protocols.
Baud Rate	1200~115200
Address	1~255
Display	
VGA	Resolution:1920*1080,1280*720,1440*900,1280*1024,1024*768
HDMI	Resolution:1920*1080,1280*720,1440*900,1280*1024,1024*768
Display Split	1/4/8/9/16 screen
Privacy Masking	4 Rectangular Zones (local camera)
OSD	Camera title, Time, Video loss, Alarm, Motion detection, Recording
Recording	
Video Compression	H.264
Audio Compression	G.711A
Resolution	1080N/720P/960H
Video Quality	Best/Better/Good/General/worse/worst
Record Rate	1080N(960×1080 16*12fps),720P(1280×720 16*13fps), 960H(P:960×576 16*25fps/N:960×480 16*30fps)
Record Mode	Manual\Timer\Motion Detection
Playback & Backup	
Sync Playback	Max 16 Channel(pure analog channel mode)
Remote Playback	4 Channel/1channel
Search Mode	ALL, Channel, Manual, Time, Date, Motion Detection
Playback Functions	Play, Pause, Stop, Rewind, Fast Play, Slow Play, Digital zoom
Backup Mode	USB Device/Network
Network	
Interface	1*RJ45 10/100 Base-T self-adaptive Ethernet port
Network Functions	DHCP、PPPOE、NTP、Email、IP Authority、DDNS、FTP、ARSP、Alarm Center、Wireless Dialing、Mobile Monitor、UPNP、Wifi、RTSP、Cloud Service
DDNS	3322、dyndns、oray、myq-see,etc
Web Browser	Internet Explorer
CMS Software	Support Windows XP /Windows Vista/Windows 7

Extra Stream	D1/CIF/QCIF(1~25fps)
Smart Phone	iPhone, Andriod
Hard Disk Driver	
Interface Type	1 SATA Interface
Capacity	Up to 6TB Capacity
General	
Language	Support 27 languages (SimChinese、TradChinese、English、Farsi、Finnish、French、German、Greek、Hungarian、Italian、Japanese、Poland、Portugal、Russian、Spanish、Thai、Turkey、Vietnamese、Romanian、Brazilian、korean、Indonesian、Swedish、Arabic、Bulgarian、Czech、Hebrew)
USB Interface	2 USB 2.0 Interfaces , supporting USB mouse
Power Supply	DC12V/2.5A
Working Environment	0°C ~ +55°C/10~90%
Dimension (WxD×H)	260*190*43(mm)
Weight	2kg