

R221Q

Part Number: UM.WR1EE.001

Technical Information

Number of Screens

1

Screen Size

54.6 cm (21.5")

Screen Mode

Full HD

Panel Technology

In-plane Switching (IPS) Technology

Response Time

4 ms

Aspect Ratio

16:9

Backlight Technology

LED

Maximum Adjustable Height

No

Swivel Angle

No

Video

Maximum Resolution

1920 x 1080

Standard Refresh Rate

60 Hz

Colour Support

16.7 Million Colours

Contrast Ratio

100,000,000:1

Audio

Speakers

Yes

Interfaces/Ports

DVI

Yes

HDMI

Yes

VGA

Yes

Power Description

Standby Power Consumption

450 mW

Off-Mode Power Consumption

400 mW

Energy Efficiency Class

A

Energy Consumption per Year

26 kWh

Operating Power Consumption (Energy Star)

22 W

Operating Power Consumption (EEL)

18 W

Physical Characteristics

Colour

Black

Height

302 mm

Width

498 mm

Depth

33.4 mm

Height with Stand

384 mm

Width with Stand

498 mm

Depth with Stand

224 mm

Weight (Approximate)

1.90 kg

Weight with Stand (Approximate)

2.30 kg

Miscellaneous

Environmentally Friendly

Yes