

Product availability : Stock - Normally stocked in distribution facility



### Main

Product	Single Throw Safety Switch
Line Rated Current	400 A
Certifications	UL listed
Enclosure Rating	NEMA 1 steel
Factory Installed Neutral	Neutral (factory installed)
Disconnect Type	Fusible disconnect
Short Circuit Current Rating	10 kA H or K 200 kA R, J or L
Mounting Type	Surface
Number of Poles	3
Electrical Connection	Lugs
Duty Rating	Heavy duty
System Voltage	600 V AC/DC
Wire Size	AWG 1/0...750 kcmil (copper or aluminium)

### Ordering and shipping details

Category	00053 - H&HU SW,NEMA1,400-1200A
Discount Schedule	DE1
GTIN	00785901451778
Nbr. of units in pkg.	1
Package weight(Lbs)	172
Returnability	Y
Country of origin	US

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1425 - Schneider Electric declaration of conformity

 Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------