

Product availability : Stock - Normally stocked in distribution facility



### Main

|                              |   |
|------------------------------|---|
| Product                      | Single Throw Safety Switch                |
| Line Rated Current           | 400 A                                     |
| Certifications               | UL listed                                 |
| Enclosure Rating             | NEMA 1 steel                              |
| Factory Installed Neutral    | None                                      |
| Disconnect Type              | Fusible disconnect                        |
| Short Circuit Current Rating | 10 kA H or K<br>200 kA R, J or L          |
| Mounting Type                | Surface                                   |
| Number of Poles              | 3   |
| Electrical Connection        | Lugs                                      |
| Duty Rating                  | Heavy duty                                |
| System Voltage               | 600 V AC/DC                               |
| Wire Size                    | AWG 1/0...750 kcmil (copper or aluminium) |

### Ordering and shipping details

|                       |                                 |
|-----------------------|---------------------------------|
| Category              | 00053 - H&HU SW,NEMA1,400-1200A |
| Discount Schedule     | DE1                             |
| GTIN                  | 00785901482192                  |
| Nbr. of units in pkg. | 1                               |
| Package weight(Lbs)   | 168                             |
| Returnability         | Y                               |
| Country of origin     | US                              |

### Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | Green Premium product   |
| RoHS (date code: YYWW)   | Compliant - since 1425 - Schneider Electric declaration of conformity |

 Schneider Electric declaration of conformity

---

|                                  |  |
|----------------------------------|--|
| REACH                            | Reference not containing SVHC above the threshold<br>Reference not containing SVHC above the threshold |
| Product environmental profile    | Available  |
| Product end of life instructions | Need no specific recycling operations  |

---

Contractual warranty

---

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---