

Product availability : Stock - Normally stocked in distribution facility



Main

Product or component type	Double Throw Safety Switch
Line Rated Current	60 A
Product certifications	UL listed
NEMA degree of protection	NEMA 12 galvanized steel
Device composition	None
Disconnecter device type	Non-fusible disconnect
Device mounting	Surface
Number of poles	4
System Voltage	600 V DC 600 V AC
AWG gauge	AWG 12...AWG 2 (aluminium) AWG 14...AWG 2 (copper)

Ordering and shipping details

Category	00134 - DT SWITCH,NEMA12
Discount Schedule	DE1
GTIN	00785901307785
Nbr. of units in pkg.	1
Package weight(Lbs)	45
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1313 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Reference not containing SVHC above the threshold

Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
