

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **019160009**
Status: **Active**
Overview: [Splices](#)
Description: Closed-End Insulated Splice for 12-22 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-19408-109-001 \(PDF\)](#)
[Product Specification PS-19902-013-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Splices
Series [19160](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
MolexKits Yes
Overview [Splices](#)
Product Name Closed-End Insulated
UPC 800753110182

Physical

Barrel Type Closed
Color - Resin Natural
Flammability 94V-2
Insulation Nylon (PA)
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.689g
Packaging Type Bag
Temperature Range - Operating 105°C
Wire Insulation Diameter 6.86mm max.
Wire Size AWG 12, 14, 16, 18, 20, 22

Electrical

Voltage - Maximum 600V

Material Info

Engineering Number NC-2212

Reference - Drawing Numbers

Packaging Specification PK-19408-109-001
Product Specification PS-19902-013-001
Sales Drawing SD-19160-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

| | |
|-----------------|---------------|
| China ROHS | Green Image |
| ELV | Not Relevant |
| RoHS Phthalates | Not Contained |

Search Parts in this Series

[19160](#) Series