

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008500114](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 254 Crimp Terminal, 22-30 AWG, Bag, Hot Tin \(Sn\) Dip Plating](#)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-001 \(PDF\)](#)
[Product Specification PS-10-07-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [2759](#)
 Application Signal
 Crimp Quality Equipment Yes
 MolexKits Yes
 Overview [KK® Interconnect System - Molex](#)
 Packaging Alternative [08-50-0113 \(Reel\)](#)
 Product Name [KK® 254](#)
 UPC 800753644595

Physical

Gender Female
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.065/g
 Packaging Type Bag
 Plating min - Mating 2.540µm
 Plating min - Termination 2.540µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.57mm max.
 Wire Size AWG 22, 24, 26, 28, 30
 Wire Size mm² N/A

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number 2759-(P909)L

Reference - Drawing Numbers

Packaging Specification PK-2759-001
 Product Specification PS-10-07-001
 Sales Drawing SD-2759



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[2759 Series](#)

Use With

[2695](#) , [5051](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION