

COMMUNICATION & CONTROL

MULTIPAIR, FOIL SHIELD
PVC/PVC

UL TYPE CM
UL AWM 2464, CSA CMG FT4
RoHS COMPLIANT, 300 VOLT

CHARACTERISTICS

OPERATING TEMPERATURE:

- -20°C to 80°C – AWM
- 75°C – CM

VOLTAGE RATING:


- 300 Volt

COLOR DESCRIPTION:

- Color Code: Chart K Page 377
- Jacket Color: Gray

PRODUCT DESCRIPTION:

- Conductor: Solid Tinned Copper
- Insulation: Color-Coded PVC
- Shield: Aluminum/Polyester, Foil Facing In
- Drain Wire: 24 AWG, 7/32 Tinned Copper
- Jacket: PVC



22 AWG (0,32mm²), Solid, Insulation Thickness: **0.013"** (0,33mm)
UL 2464 - NEC TYPE CM

Alpha Part No.	No. of Pairs	Jacket Thickness		Diameter	
		Inches	mm	Inches	mm
5902C	2	0.032	0,81	0.22	5,6
5905C	4	0.032	0,81	0.26	6,7
5906C	6	0.035	0,89	0.32	8,1
5909C	9	0.037	0,94	0.37	9,4
5909/15C	15	0.040	1,02	0.43	11,1
5909/19C	19	0.040	1,02	0.47	12,0

SPECIFICATIONS

- UL Type CM, AWM 2464
- CSA CMG FT4
- Passes UL Vertical Tray Flame Test
- RoHS Compliant



AVAILABILITY

- 100 ft (30,5m), 500 ft (152m), 1000 ft (305m) put-ups



Toll Free: 1-800-52 ALPHA • Telephone: 908-925-8000 • Fax: 908-925-6923
Europe/UK Telephone: +44 (0) 1932 772422 • Europe/UK Fax: +44 (0) 1932 772433

Web Site: www.alphawire.com
Email: info@alphawire.com