



## Vimtag | 720P Indoor Home Security Camera, Magnetic Base

### KEY FEATURES

- 100°wide-angle lens
- Two-way audio/smart Wi-Fi connection
- Android, IOS devices, remote real-time monitoring
- Multi-user access, multi-device management
- Motion detection/alarm/snapshot/video
- 64G Micro SD card / cloud box storage

SPECIFICATION	CM1
<b>CAMERA</b>	
Image Sensor	1/4 "color CMOS sensor
Display resolution	1280*720 (1.0mega pixels)
Lens	f: 3.6mm, 1.0mega pixels
Visual angle	H:60.5°; V:37°; D:72°
Min illumination	0.1Lux(IR LED OFF)
<b>AUDIO</b>	
Input/Output	Built-in microphone and speaker
Audio Compression	AAC
<b>Video</b>	
Video Compression	H.264
Lighting frequency	50Hz, 60Hz
Frame rate	25fps
Resolution	1Mega Pixels
Image adjustment	Brightness, Contrast, Saturation, Sharpness
White balance BLC	Automatically
Night vision	6 pcs matrix infrared lights, IR distance: 10 meters
<b>Network</b>	
Wireless networks	WIFI(IEEE802.12b/g/n),internal antenna
Ethernet	10/100Mbps
Protocols	TCP/IP/UDP/IP/HTTP/DHCP/RTMP/MUTP
IP address	Static IP address and dynamic IP address
<b>ALARM</b>	
Alarm detection	Motion detection
Alarm linkage	Snapshot, audio/video record, RF alarm devices
Alarm notification	Real-time App push notifications
<b>General</b>	
Power	DC 5V / 1.0 A, Micro USB interface, power consumption < 5W
Network interface	Micro USB3.0 and a special adapter
Adjustable lens	NO
LED intructions	Network signal
Video Storage	Micro SD Card* (maximum 64GB),cloud box, cloud storage
Work temperature	-10° ~ 55°C (32°F ~ 131°F)
Work humidity	10% ~ 80% (No condensation)
Storage temperature	10°C ~ 60° (14°F ~ 140°F)
Storage humidity	0% ~ 90%(No condensation)
Colour	White, Silver
Size (L*W*H)	49(L) x40(W) x111mm(H)
Weight	100g
Certificate	RoHS,CE,FCC,NCC

(\*Micro SD Card NOT supplied)