



General characteristics Samsung HM321HI

Ruler: Spinpoint M7E

Type: HDD

Purpose: laptop 2.5"

Drive specifications Samsung HM321HI

Volume: 320 GB

Buffer memory: 8 MB

Speed of rotation: 5400 rpm

Interface Samsung HM321HI

Connection: SATA 3Gb/s

External data transfer rate: 300 MB/s

Support NCQ: yes

Temporal characteristics Samsung HM321HI

Average access time, reading: 12 MS

Mechanics/Reliability Samsung HM321HI

Shock resistance at work: 400 G

Shock resistance during storage: 900 G

Noise idle: 24 dB

Operating noise level: 26 dB

Additionally Samsung HM321HI

Dimensions (WxHxL): 69.85x9.5x100 mm

Weight: 105 g