

Basic

Brand Name:	HP
DisplayPort:	Yes
Energy Star:	Yes
Environmentally Friendly:	Yes
Form Factor:	Small Form Factor
Graphics Controller	Intel
Manufacturer:	
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
Number of USB 2.0 Ports:	4
Number of USB 3.0 Ports:	4
Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro
Optical Drive Type:	DVD-Writer
Processor Manufacturer:	Intel
Processor Model:	i3-6100
Processor Speed:	3.70 GHz
Processor Type:	Core i3
Product Family:	Business Desktop ProDesk 400 G
Product Type:	Desktop Computer
Standard Memory:	4 GB
Total Hard Drive Capacity:	500 GB
Total Number of USB Ports:	8
VGA:	Yes

Display & Graphics

Graphics Controller	Intel
Manufacturer:	
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM

General Information

Brand Name:	HP
Manufacturer Part Number:	X3K60ET#ABU
Manufacturer Website Address:	http://www.hp.com
Manufacturer:	HP Inc.
Product Line:	Business Desktop
Product Name:	ProDesk 400 G3 Small Form Factor PC (ENERGY STAR)
Product Series:	ProDesk 400 G3
Product Type:	Desktop Computer

Interfaces/Ports

DisplayPort:	Yes
Number of USB 2.0 Ports:	4
Number of USB 3.0 Ports:	4
Total Number of USB Ports:	8
VGA:	Yes

Memory

Memory Technology:	DDR4 SDRAM
Standard Memory:	4 GB

Miscellaneous

Energy Star:	Yes
Environmental Certification:	REACH WEEE
Environmentally Friendly:	Yes
Features:	Security Slot
Package Contents:	<ul style="list-style-type: none">• ProDesk 400 G3 Small Form Factor PC (ENERGY STAR)• Keyboard• Mouse

Physical Characteristics

Depth:	299.7 mm
Form Factor:	Small Form Factor
Height:	269.2 mm
Weight (Approximate):	4.45 kg
Width:	94 mm

Power Description

Input Voltage: 120 V AC

Processor & Chipset

Processor Generation: 6th Gen
Processor Manufacturer: Intel
Processor Model: i3-6100
Processor Speed: 3.70 GHz
Processor Type: Core i3

Software

Operating System Architecture: 64-bit
Operating System Platform: Windows
Operating System: Windows 10 Pro

Storage

Optical Drive Type: DVD-Writer
Optical Media Supported: DVD-RAM/±R/±RW
Total Hard Drive Capacity: 500 GB

Warranty

Limited Warranty: 1 Year