

Product Color	
Product Color	Glossy Black / Texture black
Panel	
Aspect Ratio	16:9
Resolution (max.)	1920 x 1080
Display Area(mm)	527 x 296
Pixel Pitch (mm)	0.274
Brightness (Typical)	250 cd/m <sup>2</sup>
Native Contrast ( typ. )	3000:1
DCR (Dynamic Contrast Ratio) (typ.)	20M:1
Panel Type	AMVA+ (SNB)
Viewing Angle (L/R;U/D) (CR> =10)	178° / 178°
Response time	4ms (GTG)
Display Colors	16.7 Million
Color Gamut	72% NTSC
Color Bit	8bits
Backlight	LED
Regulations	
EPEAT	Silver
TCO	6.0
Energy Star	6.0
Audio/Video Inputs/Outputs	
Input Connector	D-sub / HDMI x 2
Dimensions & Weight	
Dimensions with Wall Mount (HxWxD mm) (w/o Base)	329 x 553 x 51
Dimensions(HxWxD mm)	425 x 553 x 189
Net Weight (kg)	4.0
Special Features	
AMA	Yes
HDCP	Yes
Dynamic Power Saving (DPS)	Yes
Flicker-free Technology	Yes
Color Temperature	Reddish / Normal / Bluish / User Mode
Low Blue Light	Yes

VESA Wall Mounting	100 x 100mm
Tilt (down/up)	-5°/20°
K Locker	Yes
OSD Language	17 Languages
<b>Included Accessories</b>	
Signal Cable	VGA / HDMI
<b>I/O</b>	
Headphone Jack	Yes
<b>Power</b>	
Power Supply (90~264 AC)	Built-in
Power Consumption (Power saving mode)	< 0.5W
Power Consumption (Base on Energy star )	23W
<b>Certification</b>	
Windows® 7 Compatible	Yes
Windows® 8 Compatible	Yes
Windows® 8.1 Compatible	Yes
Windows® 10 Compatible	Yes