

Operating System

Operating System

Windows 10 Pro

Processor & Chipset

Processor Manufacturer

Intel®

Processor Type

Core™ i5

Processor Model

i5-6200U

Processor Speed

2.30 GHz

Processor Core

Dual-core (2 Core™)

Memory

Standard Memory

4 GB

Maximum Memory

32 GB

Memory Technology

DDR4 SDRAM

Number of Total Memory Slots

2

Memory Card Reader

Yes

Memory Card Supported

SD

Storage

Solid State Drive Capacity

128 GB

Solid State Drive Interface

Serial ATA/600

Optical Drive Type

DVD-Writer

Display & Graphics

Screen Size

39.6 cm (15.6")

Display Screen Type

Active Matrix TFT Colour LCD

Display Screen Technology

ComfyView

Screen Mode

HD

Backlight Technology

LED

Screen Resolution

1366 x 768

Graphics Controller Manufacturer

Intel®

Graphics Controller Model

HD Graphics 520

Graphics Memory Technology

DDR4 SDRAM

Graphics Memory Accessibility

Shared

Network & Communication

Wireless LAN Standard

IEEE 802.11ac

Ethernet Technology

Ethernet

Built-in Devices

Microphone

Yes

Finger Print Reader

No

Number of Speakers

2

Sound Mode

Stereo

Interfaces/Ports

HDMI

Yes

Number of USB 2.0 Ports

1

Number of USB 3.0 Ports

2

Number of USB 3.1 Gen 1 Ports

1

Total Number of USB Ports

4

USB Connector Type

Type-C

VGA

Yes

Network (RJ-45)

Yes

Software

Operating System

Windows 10 Pro

Operating System Architecture

64-bit

Input Devices

Pointing Device Type

TouchPad

Keyboard

Yes

Battery Information

Number of Cells

4-cell

Battery Chemistry

Lithium Ion (Li-Ion)

Battery Capacity

2800 mAh

Power Description

Maximum Power Supply Wattage

45 W

Physical Characteristics

Height

30.2 mm

Height (Front)

23.90 mm

Height (Rear)

30.20 mm

Width

381.6 mm

Depth