


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0502178000**
Status: **Active**
Description: 3.50mm Pitch Crimp Terminal 50217, 18-24 AWG, Reel, Phosphor Bronze

Documents:

3D Model	Product Specification PS-51067-018 (PDF)
Drawing (PDF)	Product Specification PS-51067-022-001 (PDF)
Product Specification PS-51067-003 (PDF)	Product Specification PS-51067-023-001 (PDF)
Product Specification PS-51067-004 (PDF)	Packaging Specification SPK-50217-001-001 (PDF)
Product Specification PS-51067-006 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Terminals
Series	<u>50217</u>
Application	Signal
Crimp Quality Equipment	Yes
Packaging Alternative	<u>50217-8100</u> (Loose)
Product Name	N/A
UPC	800753576148

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	160.000/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40-3.00mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm ²	N/A

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-50217-001-001
Product Specification	PS-51067-003, PS-51067-004, PS-51067-006, PS-51067-018, PS-51067-022-001, PS-51067-023-001
Sales Drawing	SD-50217-****

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

50217 Series

Mates With

50419

Use With

51067