

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0192020013**
Status: **Active**
Overview: Splices
Description: NylaKrimp™ Butt Splice for 18-22 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Splices
Series 19202
Crimp Quality Equipment Yes
Mil-Spec N/A
MolexKits Yes
Overview Splices
Product Name Butt, NylaKrimp™
UPC 800753047396

Physical

Barrel Type Closed - Brazed
Color - Resin Red
Flammability 94V-2
Insulation Nylon (PA)
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 1.047/g
Packaging Type Bag
Temperature Range - Operating -55°C to +105°C
Wire Insulation Diameter 3.56mm max.
Wire Size AWG 18, 20, 22
Wire Size mm² 0.35-0.80

Electrical


Voltage - Maximum 600V

Material Info

Engineering Number AS-N-345

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
Sales Drawing 60002-11C



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19202 Series