

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0561348100**
Status: **Active**
Overview: MicroClasp™ Wire-to-Board System
Description: 2.00mm Pitch Crimp Terminal 56134, Female, 22-26 AWG, Bag, Phosphor Bronze, for 51242/51353/51382 Housings

Documents:

3D Model	Application Specification 5055960001-001 (PDF)
Drawing (PDF)	Packaging Specification SPK-56134-001-001 (PDF)
Application Specification 5055960001-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	<u>56134</u>
Application	Signal
Crimp Quality Equipment	Yes
Overview	<u>MicroClasp™ Wire-to-Board System</u>
Product Name	MicroClasp™
UPC	800756190549


Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	36.000/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.25-1.70mm
Wire Size AWG	22, 24, 26
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Application Specification	5055960001-000, 5055960001-001
Packaging Specification	SPK-56134-001-001
Sales Drawing	SD-56134-002



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

56134 Series

Use With

51242 Dual Row Crimp Housing, 51353 Dual Row Crimp Housing, 51382 Single Row Crimp Housing