

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008560106](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 396 Crimp Terminal 2478, 18-24 AWG, Bag, Brass, 0.51µm Selective Gold \(Au\)](#)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-001 \(PDF\)](#)
[Product Specification PS-08-50-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
Series [2478](#)
Application [Power](#)
Crimp Quality Equipment [Yes](#)
Overview [KK® Interconnect System - Molex](#)
Packaging Alternative [08-56-0105 \(Reel\)](#)
Product Name [KK® 396, KK® 508](#)
UPC [800753614215](#)

Physical

Gender [Female](#)
Material - Metal [Brass](#)
Material - Plating Mating [Gold](#)
Material - Plating Termination [Gold](#)
Net Weight [0.150/g](#)
Packaging Type [Bag](#)
Plating min - Mating [0.381µm](#)
Plating min - Termination [0.051µm](#)
Termination Interface: Style [Crimp or Compression](#)
Wire Insulation Diameter [2.79mm max.](#)
Wire Size AWG [18, 20, 22, 24](#)
Wire Size mm² [N/A](#)

Solder Process Data

Lead-freeProcess Capability [N/A](#)

Material Info

Engineering Number [2478-1-\(550\)L](#)

Reference - Drawing Numbers

Packaging Specification [PK-2759-001](#)
Product Specification [PS-08-50-001](#)
Sales Drawing [SD-2478](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[2478 Series](#)

Use With

[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) , [5239](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION