


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0050579004**  
**Status:** **Active**  
**Overview:** SL™ Modular Connectors  
**Description:** SL™ Crimp Housing, Single Row, Version A, Non-polarized, 4 Circuits

**Documents:**

|  |  |
|--|--|
| <a href="#">3D Model</a>                                 | <a href="#">Product Specification TS-70058-001-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                            | <a href="#">Product Specification TS-70541-001-001 (PDF)</a> |
| <a href="#">Product Specification PS-70058-001 (PDF)</a> | <a href="#">Packaging Specification PK-70066-100 (PDF)</a>   |
| <a href="#">Product Specification PS-70400-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>         |
| <a href="#">Product Specification PS-71851-001 (PDF)</a> |  |



**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |                               |
|----------------|-------------------------------|
| Product Family | Crimp Housings                |
| Series         | <u>70066</u>                  |
| Application    | Signal, Wire-to-Board         |
| Comments       | Version A                     |
| Overview       | <u>SL™ Modular Connectors</u> |
| Product Name   | SL™                           |
| UPC            | 800753578180                  |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Circuits (maximum)            | 4               |
| Color - Resin                 | Black           |
| Flammability                  | 94V-0           |
| Gender                        | Female          |
| Glow-Wire Compliant           | No              |
| Keying to Mating Part         | None            |
| Lock to Mating Part           | No              |
| Material - Resin              | Polyester Alloy |
| Net Weight                    | 0.029/g         |
| Number of Rows                | 1               |
| Packaging Type                | Bag             |
| Panel Mount                   | No              |
| Pitch - Mating Interface      | 2.54mm          |
| Stackable                     | Yes             |
| Temperature Range - Operating | -40°C to +105°C |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 3.0A |
|-------------------------------|------|

**Solder Process Data**

|                              |     |
|------------------------------|-----|
| Lead-free Process Capability | N/A |
|------------------------------|-----|

**Material Info**

|                    |            |
|--------------------|------------|
| Engineering Number | 70066-0003 |
|--------------------|------------|

**Reference - Drawing Numbers**

|                         |  |
|-------------------------|--|
| Packaging Specification | PK-70066-100   |
| Product Specification   | PS-70058-001, PS-70400-001, PS-71851-001, TS-70058-001-001, TS-70541-001-001 |
| Sales Drawing           | SD-70066-0001-0024   |

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2017 (12  
January 2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**

70066 Series

**Mates With**

42375 , 42377 , 70280 , 70287 , 71308 , 70543 , 70553

**Use With**

SL™ Crimp Terminal 70058 , 71851

This document was generated on 02/15/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**