

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008550102](#)
Status: **Active**
Overview: KK® Interconnect System - Molex
Description: KK® 254 Crimp Terminal, 22-30 AWG, Bag, Selective Gold (Au), Nickel (Ni) Under Plating

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-001 \(PDF\)](#)
[Product Specification PS-10-07-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
 Series 2759
 Application Signal
 Crimp Quality Equipment Yes
 Overview KK® Interconnect System - Molex
 Packaging Alternative 08-55-0101 (Reel)
 Product Name KK® 254
 UPC 800753745995

Physical

Gender Female
 Material - Metal Brass
 Material - Plating Mating Gold
 Material - Plating Termination Nickel
 Net Weight 0.064/g
 Packaging Type Bag
 Plating min - Mating 0.381µm
 Plating min - Termination 0.762µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.57mm max.
 Wire Size AWG 22, 24, 26, 28, 30
 Wire Size mm² N/A

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number 2759-(555)L

Reference - Drawing Numbers

Packaging Specification PK-2759-001
 Product Specification PS-10-07-001
 Sales Drawing SD-2759



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2017 (12
 January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[2759 Series](#)

Use With

[2695](#) , [5051](#)