

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0357460210**
Status: **Active**
Overview: VersaBlade™ Wire-to-Wire Connector System
Description: VersaBlade™ .070 Female Crimp Terminal, 14-18 AWG, Type A

Documents:

3D Model	Product Specification PS-35180-003 (PDF)
Drawing (PDF)	Product Specification PS-35182-003-001 (PDF)
Product Specification PS-35150-001-001 (PDF)	Packaging Specification PK-35746-001-001 (PDF)
Product Specification PS-35180-002 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	<u>35746</u>
Application	Power
Crimp Quality Equipment	Yes
Overview	<u>VersaBlade™ Wire-to-Wire Connector System</u>
Product Name	VersaBlade™
UPC	800754378468

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.320/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.80mm max.
Wire Size AWG	14, 18
Wire Size mm²	N/A


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35746-001-001
Product Specification	PS-35150-001-001, PS-35180-002, PS-35180-003, PS-35182-003-001
Sales Drawing	SD-35746-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

35746 Series

Mates With

35745 Crimp Terminal

Use With

35150 VersaBlade™ Hybrid Receptacle Housing. 35151 VersaBlade™ Hybrid Plug Housing