

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0366630001](#)
Status: **Active**
Overview: [MLX™ Power Connectors](#)
Description: [MLX™ Double Crimp Terminal, 10-12 AWG, Reel, Tin \(Sn\)](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-36663-001-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	36663
Application	Power
Comments	Current – Maximum per contact 20A if used with 36663 and 36664 terminal
Crimp Quality Equipment	Yes
Overview	MLX™ Power Connectors
Packaging Alternative	36663-0002 (Loose)
Product Name	MLX™
UPC	822348359387

Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.385/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	5.08mm max.
Wire Size AWG	10, 12
Wire Size mm²	3.30, 5.25

Electrical

Current - Maximum per Contact	20.0A
-------------------------------	-------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Product Specification	PS-36663-001-001
Sales Drawing	SD-36663-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[36663 Series](#)

Use With

42021 Plug, 42022 Receptacle. MLX
Double Crimp Terminal [36663](#) , MLX Crimp
Terminal [36664](#)