

## Zack Marker strip, flat - ZBF 12:UNBEDRUCKT - 0809735

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, Mounting type: Snap into flat marker groove, for terminal block width: 12 mm, Lettering field: 5.15 x 12.15 mm

The illustration shows the 15 mm wide version

### Why buy this product

- Can be labeled with CMS computer marking system or by hand using B-STIFT
- Sealing caps with external or inner thread
- Printed or unprinted marking labels
- Consists of five individual labels with 17.5 mm pitch
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- Flat zack marker strips

### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
GTIN	 4 017918 591694
GTIN	4017918591694
Weight per Piece (excluding packing)	0.660 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Dimensions

Width (a)	12 mm
-----------	-------

## Zack Marker strip, flat - ZBF 12:UNBEDRUCKT - 0809735

### Technical data

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

#### General

Color	white
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	5
Number of individual labels per row	5
Number of marker strips	5
Marking mounting type	Snap into flat marker groove

#### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2