

Specification

Photo	
Capacity	2GB-32GB
Color	Claret Red
Interface	USB 2.0 certified, backward compatible with USB 1.1 True "plug & play" supports hot swapping function
Power Supply	USB Bus-Powered; No external power required
Systems Supported	Windows 10/8.1/8/7/XP Mac OS 10.4.X or above Linux 2.6.X or above
Operating Temperature	0° C to +60° C (32° F to 140° F)
Storage Temperature	-20° C to +60° C (-4° F to +140° F)
Dimensions	(L) 60.8 x (W) 18.8 x (H) 8 mm
Weight	8g approx.