

# C2SS1-10B-20



Products Low Voltage Products and Systems Control Products Pilot Devices Pilot Devices - Compact Range

## General Information

<b>Extended Product Type:</b>	C2SS1-10B-20
<b>Product ID:</b>	1SFA619200R1026
<b>EAN:</b>	7320500245408
<b>Catalog Description:</b>	SELECTOR SWITCH#C2SS1-10B-20
<b>Long Description:</b>	Compact Selector Switch - 2-pos Fixed B&C - Short handle - Black - Non-illuminated - Black plastic - 2NO

## Additional Information

<b>ABB Industrial IT Suite:</b>	Control IT
<b>Actuator Type:</b>	Short handle
<b>Ambient Air Temperature:</b>	Storage -30 ... +85 °C Operation -25 ... +70 °C
<b>Bezel Material:</b>	Black plastic
<b>Block:</b>	2NO
<b>Color:</b>	Black
<b>Country of Origin:</b>	China (CN)
<b>Customs Tariff Number:</b>	85369001
<b>Data Sheet, Technical Information:</b>	1SFC151003C0201
<b>Declaration of Conformity - CE:</b>	1SFA1-70
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
<b>E-nummer:</b>	3705527
<b>EAN:</b>	7320500245408
<b>ETIM 4:</b>	EC002024 - Accessories for control circuit devices
<b>ETIM 5:</b>	EC001029 - Selector switch, complete
<b>ETIM 6:</b>	EC001029 - Selector switch, complete
<b>Environmental Information:</b>	1SFC151009D0201
<b>Function:</b>	Maintained
<b>IT Publishing Status:</b>	Level 0 - Information enabled
<b>Illumination:</b>	Non-illuminated
<b>Industrial IT Certification Level:</b>	0
<b>Instructions and Manuals:</b>	1SFC151003C0201
<b>Invoice Description:</b>	SELECTOR SWITCH#C2SS1-10B-20
<b>Maintained Positions:</b>	B, C
<b>Mechanical Durability:</b>	0.5 million
<b>Minimum Order Quantity:</b>	10 piece
<b>Number of Auxiliary Contacts NO:</b>	2
<b>Object Classification Code:</b>	S
<b>Package Level 1 Gross Weight:</b>	0.024 kg
<b>Package Level 1 Height:</b>	0.03 m
<b>Package Level 1 Length:</b>	0.1 m
<b>Package Level 1 Units:</b>	10 piece
<b>Package Level 1 Width:</b>	0.1 m
<b>Package Level 2 Units:</b>	10
<b>Product Main Type:</b>	C2SS1
<b>Product Name:</b>	Selector Switch

<b>Product Net Depth:</b>	0.072 m
<b>Product Net Height:</b>	0.030 m
<b>Product Net Weight:</b>	0.024 kg
<b>Product Net Width:</b>	0.030 m
<b>Product Range:</b>	Compact
<b>Product Type:</b>	C2SS
<b>Rated Frequency (f):</b>	Supply Circuit 60 Hz Supply Circuit 50 Hz
<b>Rated Operational Current AC-15 (I<sub>e</sub>):</b>	(24 / 127 V) 1.5 A (220 / 240 V) 1 A
<b>Rated Operational Current DC-13 (I<sub>e</sub>):</b>	(24 V) 0.3 A (125 V) 0.2 A
<b>RoHS Date:</b>	0626 5
<b>RoHS Information:</b>	1SFC151012D0202
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	Black Compact Selector Switch
<b>Sub-Function:</b>	2-position
<b>UNSPSC:</b>	39121500