

NITRO 4x5

4 CHN 1080P HI-DEF TVI, AHD, 960H, IP, CVI - NVR

HDMI

Full HD
1080P



5 In 1 Formats

This NVR supports High-Definition Transport Video (HD-TVI), Analogue High Definition (AHD), 960H, Internet Protocol (IP) and High Definition Composite Video Interface (CVI) recording formats.



Widescreen Footage

1080P formatting also means that images are recorded in a widescreen format which suits modern TV's and monitors, meaning images do not get stretched or squeezed to fit on screen.



Scheduled Recording

Set the NVR to record at specific times of the day or for set periods when you are at work, away for weekends or on holiday.

NITRO 4x5

NITRO NVR KEY FEATURES

- Support 4ch 4M unreal-time encoding
- Support VGA maximum 1080P output, HDMI up to 2K output
- Mini 1U Case, 1 SATA (Up to 6TB)
- 1*10/100Mbps auto-sensing Ethernet port, RJ45 port
- Automatic networking support, a key to add equipment
- Support the Onvif protocol
- Multi browser access
- Support for more than twenty languages

NITRO 4x5

4 CHN 1080P HI-DEF TVI, AHD, 960H, IP, CVI - NVR



Model	4x5-4 Channel
VIDEO	
Video Codec	H.264
Encode	4*4M@8fps(AHD); 4*3M@10fps(AHD); 4*1080P@15fps(5 in 1); 4*720P(5 in 1)
Decode	4*4M@8fps(AHD); 4*3M@10fps(AHD); 4*1080P@15fps(5 in 1); 4*720P(5 in 1)
Multi-mode	Analog 4*4M@8fps(AHD); 4*3M@10fps(AHD); 4*1080P@15fps(5 in 1); 4*720P(5 in 1). Hybird 2*4M (analog) +2*4M (network). IP 16*1080P; 9*1080P; 16*960P; 4*5M.
Preview	4*4M@15fps(AHD); 4*3M@18fps(AHD); 4*1080P(5 in 1)
AUDIO	
Audio Compression	G.711a
Intercom	Support
RECORDING AND PLAYBACK	
Record Mode	Manual>Alarm>Motion detection>Timing
Inquire Mode	Inquire by Time/Calendar/Event/Channel
Playback Channels	4 Channel
STORAGE	
Storage Mode	HDD Storage, Network Storage
Backup	Network, USB, SATA
INTERFACE	
Video Input	4*BNC (Support Coaxitron)
Video Output	1*HDMI (MAX:2K), 1*VGA (MAX:1080P)
Audio Input/Output	4/1
Alarm Input/Output	0/0
Ethernet Port	1*10/100Mbps Ethernet port, RJ45 port
PTZ Control	1*RS485, Support for multiple PTZ protocol
USB Port	2*USB 2.0 ports
Hard Disk	1*SATA interface (Up to 6TB)
GENERAL	
Temperature	0°C- + 55°C
Humidity	10% -90% RH
Power Supply	12V/2A
Consumption	<10W (Without HDD)
Weight	Around 1KG
Dimension	255mm(L)* 236mm(W)* 44mm(H)

