

# NITRO 4x5

8 CHN 1080P HI-DEF TVI, AHD, 960H, IP, CVI - NVR



## 5 In 1 Formats

This NVR supports High-Definition Transport Video (HD-TVI), Analogue High Definition (AHD), 960H, Internet Protocol (IP) and High Definition Composite Video Interface (CVI) recording formats.



## Widescreen Footage

1080P formatting also means that images are recorded in a widescreen format which suits modern TV's and monitors, meaning images do not get stretched or squeezed to fit on screen.



## Scheduled Recording

Set the NVR to record at specific times of the day or for set periods when you are at work, away for weekends or on holiday.

# NITRO 4x5

## NITRO 4X5 NVR KEY FEATURES

- P2P No Port Forwarding
- Real Time 1080P Recordings
- HDMI/VGA Monitor Outputs
- PTZ Control
- USB Backup
- Motion Detection
- 4 Channel Playback
- 4 Alarm Inputs
- Arc Compatible
- 5-in-1 NVR

# NITRO 4x5

8 CHN 1080P HI-DEF TVI, AHD, 960H, IP, CVI - NVR



|                               |  |
|-------------------------------|--|
| <b>Model</b>                  | <b>4x5-8 Channel</b>   |
| <b>VIDEO</b>                  |  |
| Video Codec                   | H.264  |
| Encode                        | 8*4M@6fps(AHD); 8*3M@8fps(AHD); 8*1080P@12fps(5-in-1)              |
| Decode                        | 4*4M@6fps(AHD); 4*3M@8fps(AHD); 4*1080P@12fps(5-in-1)              |
| Multi-mode Input              | Pure Analog: 8*1080P<br>Pure Network: 8*1080P; 16*960P; 4*3M; 4*5M |
| Onvif                         | Support  |
| <b>AUDIO</b>                  |  |
| Audio Compression             | G.711A   |
| Intercom                      | Support  |
| <b>RECORDING AND PLAYBACK</b> |  |
| Record Mode                   | Manual>alarm>motion detection>timing                               |
| Playback Channels             | 4 (pure local input mode)  |
| <b>STORAGE</b>                |  |
| Backup Mode                   | Network backup, USB HDD, USB writer, SATA writer                   |
| <b>INTERFACE</b>              |  |
| Video Input                   | 8 BNC  |
| Video Output                  | 1ch VGA, 1ch HDMI  |
| Audio Input                   | 8ch RCA  |
| Audio Output                  | 1ch RCA  |
| Alarm Input                   | 4  |
| Alarm Output                  | 1  |
| Network Interface             | RJ45 10M/100M Adaptive Ethernet port                               |
| PTZ Control                   | RS485; Support multiple PTZ protocols                              |
| USB                           | 2 USB ports  |
| Hard Disk                     | 1 SATA (Each maximum support 6T)                                   |
| Power                         | 12V/2A   |
| Dimension                     | 310mm (Length) x 230mm (Width) x 44mm (Height)                     |

HDMI

Full HD  
1080P



NITRO  
4x5

