




LFT58WH: 345mm 21mm 43mm
 LFT513WH: 570mm
 LFT521WH: 900mm
 LFT528WH: 1200mm

LFT58WH shown

Eterna LFT5 8W/13W



This luminaire is compatible with bulbs of the energy classes:



This luminaire is sold with a bulb of the energy class: **A**


874/2012



Eterna LFT5 21W/28W



This luminaire is compatible with bulbs of the energy classes:



This luminaire is sold with a bulb of the energy class: **A+**

874/2012



ENERGY LABEL
 Y IJA IE IA
 енергия · ενεργεια

Eterna 8W

A

8.80 kWh/1000h

ENERGY LABEL
 Y IJA IE IA
 енергия · ενεργεια

Eterna 13W

A

14.30 kWh/1000h

ENERGY LABEL
 Y IJA IE IA
 енергия · ενεργεια

Eterna 21W

A+

22.66 kWh/1000h

ENERGY LABEL
 Y IJA IE IA
 енергия · ενεργεια

Eterna 28W

A+

30.69 kWh/1000h

| LAMP SPECIFICATIONS: | LFT5 21WH | LFT5 28WH |
|---|---|---|
| Nominal Wattage | 21W | 28W |
| Rated Wattage | 20.6W | 27.9W |
| Average lifetime hours | 24,000 hrs | 24,000 hrs |
| Nominal useful luminous flux | 1890 lm | 2604 lm |
| Rated luminous flux | 1890 lm | 2604 lm |
| Luminous efficacy (Lm/W) in HF operation | 90 | 93 |
| Rated lamp Lumen maintenance in HF operation | 2000hrs: 95% 4000 hrs: 92% 6000 hrs: 90% 8000 hrs: 90% 12000 hrs: 90% 16000 hrs: 90% | 2000hrs: 95% 4000 hrs: 92% 6000 hrs: 90% 8000 hrs: 90% 12000 hrs: 90% 16000 hrs: 90% |
| Rated survival factors in HF operation | 2000hrs: 99% 4000 hrs: 97% 6000 hrs: 92% 8000 hrs: 92% 12000 hrs: 90% 16000 hrs: 90% | 2000hrs: 99% 4000 hrs: 97% 6000 hrs: 92% 8000 hrs: 92% 12000 hrs: 90% 16000 hrs: 90% |
| Lamp dimensions (mm) | 850mm | 1150mm |
| Cap type | G5 | G5 |
| Lamp Mercury content to an accuracy of 0.1mg | ≤2.7mg | ≤2.7mg |
| Colour rendering index Ra | ≥80 | ≥80 |
| Colour temperature | 3500K | 3500K |
| Ambient temperature required to achieve maximum luminous flux | 25°C | 25°C |
| Dimmable | No | No |

T5 LINKABLE FLUORESCENT FITTINGS

- 8W requires 1 x 8W G5 T5 300mm fluorescent tube (included). Fitting is rated at 8W max
- 13W requires 1 x 13W G5 T5 525mm fluorescent tube (included). Fitting is rated at 13W max
- 21W requires 1 x 21W G5 T5 850mm fluorescent tube (included). Fitting is rated at 21W max
- 28W requires 1 x 28W G5 T5 1150mm fluorescent tube (included). Fitting is rated at 28W max
- **8/13W:** This luminaire is compatible with bulbs of the energy classes: A to E and is sold with a bulb of the energy class: A
- **21/28W:** This luminaire is compatible with bulbs of the energy classes: A+ to E and is sold with a bulb of the energy class: A+
- Polycarbonate construction • Rocker switch • Reeded diffuser
- High frequency electronic ballast: instant start, flicker free operation, and prolonged lamp life
- Incorporates plug and socket with through wiring: can be linked with up to 5 other fittings
- Complete with 2 metres of mains lead, 500mm link lead and butting connector: easy installation
- Not compatible with link & light series fittings & accessories

- **8W** = M.O.M: 5 / O.P.Q: 40
- **13/21/28W** = M.O.M: 5 / O.P.Q: 20

| Code | Colour | Wattage | Colour Temp. | Lumens | Avg. Rated Life (Hrs) | IP Rating | Energy Rating |
|----------|--------|---------|--------------|---------|-----------------------|-----------|---------------|
| LFT58WH | White | 8W | 3500K | 448 lm | 8,000 hrs | IP20 | A |
| LFT513WH | White | 13W | 3500K | 806 lm | 8,000 hrs | IP20 | A |
| LFT521WH | White | 21W | 3500K | 1890 lm | 24,000 hrs | IP20 | A+ |
| LFT528WH | White | 28W | 3500K | 2604 lm | 24,000 hrs | IP20 | A+ |

