


18W AC-DC Interchangeable Power Supplies

- FR4 PCB
- 100% ATE Tested
- High Reliability
- Built in OVP, OCP & SCP
- 100% smart burn-in test for 4 hours
- Level VI Efficiency Regulations Compliant
- Universal Input 90~260V AC 47~63Hz



DIMENSIONS



15DYS618

SPECIFICATIONS

Input	Input Range	100~240VAC (Full Range), 50/60Hz
	Input Current (RMS)	0.5A@90VAC 0.2A@264VAC
Output	Voltage Range	4~24VDC
	Voltage Regulation	+/- 5% At Constant Voltage Mode
	Current Range	0.1~3.5A
	Max Power	18W
Energy Saving		NRCAN, DOE, ERP, GEMS, Efficiency Level VI
Environmental Protection		RoHS, REACH, PAHS
Environmental	Operating Temperature	0°C ~45°C Ambient
	Storage Temperature	-20°C ~+80°C
	Operating Humidity	10~90% (Non-condensing)
	Relative Humidity	5~95% (Non-condensing)
	MTBF	>25,000 hours at 80% load and 25°C ambient temperature
Approvals		cETLus, TUV-GS, RCM (C-Tick), PSE, CCC, CB, FCC, CE, RoHS & REACH