

## Hospital-Grade Computer Power Cord with Clear Plugs, 13A, 16 AWG (NEMA 5-15P to IEC-320-C13), 3 ft.

MODEL NUMBER: **P006-003-HG13CL**



### Highlights

- Conforms to hospital-grade power cord standards
- Tested to ANSI/UL 62 and 817 and CAN/CSA C22.2 no. 21 and 49
- 125V/13A rating
- Fully molded ends
- Clear C13 and NEMA 5-15P-HG hospital-grade plugs

### Package Includes

- P006-003-HG13CL  
Hospital-Grade Computer Power Cord, 3 ft.

### Description

The P006-003-HG13CL Hospital-Grade Computer Power Cord features a C13 plug on one end and a NEMA 5-15P-HG plug on the other, allowing you to connect your computer or peripheral to a hospital-grade AC power outlet. Both plugs are clear, so you can inspect their internal construction at a glance. The unit is tested to ANSI/UL 62 and 817, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a safe, reliable power solution for hospital environments. The C13 plug connects to computers, printers, scanners, monitors and other electronic devices with a three-pin C14 port. This three-foot 125V/13A cord features 16 AWG, a flexible SJT jacket and fully molded ends for optimum performance.

### Features

#### Safe, Reliable Power Solution for Hospital Environments

- Connects computers and peripherals to a grounded hospital-grade AC outlet
- Ideal for replacing an old or lost cord
- Features C13 female connector and NEMA 5-15P-HG male connector
- Clear plugs for visual inspection of internal construction
- Conforms to hospital-grade power cord standards

#### Optimum Construction

- Tested to ANSI/UL 62 and 817 and CAN/CSA C22.2 no. 21 and 49
- 16 AWG
- Flexible SJT jacket
- Fully molded ends
- 125V/13A rating

## Specifications



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>INPUT</b>	
Cable Length (ft.)	3
Cable Length (m)	0.9
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
<b>CERTIFICATIONS</b>	
Certifications	ANSI/UL 62 AND 817, CAN/CSA C22.2 NO. 21 AND 49, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>