



Business Desktop 280 G2 Desktop Computer

Take on your everyday work at an affordable price with the HP 280 SFF. Get the computing power you need while minimizing the PC footprint and the total cost of ownership—now that's a smart investment.

- Windows 10 Pro or other operating systems available

Ready for work

The HP 280 SFF provides a powerful PC with the features you need to accomplish your everyday tasks.

Progressive style

Take up less space than a traditional tower with the HP 280 SFF with a stylish design that is easy to set up and use.

Powered up processing

Keep up with daily tasks with strong performance from an Intel® Core™ i3/i5 processor, Intel HD Graphics, and up to 32 GB of DDR4 memory.

Customize for collaboration

Accessorize the HP 280 SFF with the right products to customize your system for collaboration. With the HP Collaboration Keyboard and the HP Stereo 3.5mm Headset you can communicate clearly with colleagues.

Featuring

Let nothing stand in your way

- Help secure the future of your business. PCs from HP make the most of Windows 10 Pro to protect you from today's security threats and maximize management and productivity features for business.

Eight USB ports

- Connect peripherals and devices via an HDMI port, a VGA port, two front USB, and six rear USB ports.

Cloud-based IT management made simple

- Manage data, security, and devices from a single cloud-based solution with HP Touchpoint Manager.

PC management made more manageable

- Spend less time and get right to the updates you need with HP Support Assistant.

Clean software image

- With the clean, professional software image on the HP 280 SFF, you will be productive in no time!

Simple wireless printing

- Make better use of your workspace. HP ePrint makes wireless printing simple, no need for drivers.

Accidents happen. HP can help.

- Optional HP Care Packs with Accidental Damage Protection helps you avoid out-of-pocket repair or replacement costs and delivers service right to your door.
- Windows 10 Pro or other operating systems available

Manufacturer Part Number

Z6S48EA#ABU

Full Product Specifications

Note:

- *The full product specifications below are from the manufacturer and may contain information related to other package quantities that will not apply to the product that you are reviewing. Please confirm the actual content and/or package quantity from the main product specifications page.*
- *These specifications may represent the entire product series/model/line to which this product belongs with specific configuration differences between the individual products stated.*
- *These specifications may have been copied from the same product in other region/country in which case there might be minor differences in region-specific data such as Input Voltage, Terms of Warranty etc.*

System features : Operating system: Windows 10 Pro 64 – HP recommends Windows 10 Pro. ¹

Windows 10 Home 64 ¹

FreeDOS 2.0

Processor family: Intel® Core™ i5 processor

Intel® Core™ i3 processor

Intel® Pentium® processor

Intel® Celeron® processor

Processor: Intel® Core™ i5-6500 with Intel HD Graphics 530 (3.2 GHz, up to 3.6 GHz with Intel Turbo Boost, 6 MB cache, 4 cores)

Intel® Core™ i3-6100 with Intel HD Graphics 530 (3.7 GHz, 3 MB cache, 2 cores)

Intel® Pentium™ G4400 with Intel HD Graphics 510 (3.3 GHz, 3 MB cache, 2 cores)

Intel® Celeron™ G3900 with Intel HD Graphics 510 (2.8 GHz, 2 MB cache, 2 cores) ²

Chipset: Intel® H110

Form factor : Small form factor

Memory : Maximum memory: 32 GB DDR4-2133 SDRAM

(Transfer rates up to 2133 MT/s)

Memory slots : 2 DIMM

Storage : Internal drive bays: One 3,5 cm (2.5") HDD; One 8,9 cm (3.5") HDD

External drive bays : One Slim ODD (optional); 1 SD reader

Internal drive: 500 GB up to 1 TB SATA (7200 rpm) ⁴

128 GB SATA SSD ⁴

Optical drive: Slim SATA DVD-ROM

Slim SATA DVD-Writer ⁵

Display and graphics : Graphics: Integrated:

Intel® HD GraphicsDiscrete:

NVIDIA® GeForce® GT 730 (2 GB)(Integrated graphics will depend on processor)

Expansion features : Ports: Front:

2 USB 3.0

1 microphone/headphone combo

Back:

6 USB 2.0

1 audio line in

1 audio line out

1 HDMI

1 VGA

1 RJ-45

Expansion slots: 1 PCIe x1

1 PCIe x16

Media devices : Audio: HD audio with Realtek ALC3252 codec, combo microphone/headphone jack and 3.5 mm line-out and line-in ports

Communications : Network interface:

LANIntegrated Realtek RTL8111HSH-CG GbE

WLANIntel® 3168 802.11ac wireless with PCIe caddy card and Bluetooth®

Intel® 3168 802.11ac wireless with PCIe caddy card ⁶

Power and operating requirements : Energy efficiency: ENERGY STAR® certified and EPEAT® registered configurations available ⁹

Power supply:

- 180 W, up to 85% efficient, active PFC

Dimensions and weight : Dimensions (W x D x H): (270 x 290 x 100 mm)

Weight: (3.66 kg)

(Configured with 1 HDD and 1 ODD. Exact weight depends on configuration)

Security management : Security management: Trusted Platform Module (TPM) 2.0 (firmware)

Security cable slot

What's included : Software: HP business PCs are shipped with a variety of software titles including Cyberlink Power Media Player, Cyberlink Power2Go (secure burn), HP ePrint Driver, HP Recovery Manager and HP Support Assistant. Please refer to this product's quick spec document for a full list of preinstalled software. ⁸

Warranty : On-site warranty: One-year (1-1-1) limited warranty delivers one year of on-site, next business day service for parts and labor and includes free telephone support 24 x 7. One-year onsite and labor are not available in all countries. Service offers terms up to 5 years by choosing a Care Pack. To choose the right level of service for your HP product, visit HP Care Pack Central: www.hp.com/go/cpc

Z6S48EA#ABU

Product Data Powered by  GfK