

# USB Charging Receptacles Type-C • Type A&C • Type A

**HUBBELL**<sup>®</sup>  
Wiring Device-Kellems

## Charger Outlets

Next Generation  
in Technology  
USB Type-C



The Charging Choice



Type-C



Type A&C



Type A

Charge Faster with Hubbell



# USB Charging Receptacles

## Type-C • Type A&C • Type A

**HUBBELL®**  
Wiring Device-Kellems

Hubbell USB Chargers are available in the new Type-C port, a combination unit with Type A and C, and the legacy Type A, all with more power. The increase in power to a 5 Amp 5 Volt USB port adds capacity so that there is always ample current to support multiple device charging. Portable mobile manufacturers recently announced products using the faster Type-C ports. More phones, tablets and other electronic devices are expected to use this new standard.

The USB Charger delivers USB power eliminating the need for adapters, while maintaining electrical outlets for higher current requirements. The new USB standard Type-C port supports faster mobile device charging. Hubbell offers more charging options with Type-C and Type A USB configurations.

### USB Charger Features

- Compliant with USB BC1.2 Battery Charging and 3.0 Power delivery. Compatible with USB 2.0, 3.0 and 3.1 devices.
- USB Type-C port is legacy USB Type A compatible (with adapter cord - not included).
- Heavy duty stainless steel USB ports; rated for 10,000 cord insertions and removals.
- Patented Hubbell Tamper-Resistant technology uses cam action shutters. When two plug blades are inserted the interlocked cams slide an insulating barrier out of the way. The friction-free design of the mechanism's doors requires much less force, allowing the plug to slide in effortlessly.
- Designed for commercial, industrial and home use.



### USB Charger Type-C

Description	Color	15A 125V	20A 125V
USB Charger Outlet:	Black	<b>USB15C5BK</b>	<b>USB20C5BK</b>
two Type-C port configurations,	Brown	<b>USB15C5</b>	<b>USB20C5</b>
high power 5 Amp, 5 Volt USB output,	Gray	<b>USB15C5GY</b>	<b>USB20C5GY</b>
USB ports rated 10,000 cycles	Ivory	<b>USB15C5I</b>	<b>USB20C5I</b>
Commercial Grade Tamper-Resistant duplex receptacle	Light Almond	<b>USB15C5LA</b>	<b>USB20C5LA</b>
	White	<b>USB15C5W</b>	<b>USB20C5W</b>



USB15C5W

### USB Charger Combination Type A&C

Description	Color	15A 125V	20A 125V
USB Charger Outlet:	Black	<b>USB15AC5BK</b>	<b>USB20AC5BK</b>
one Type A and one Type-C port configurations,	Brown	<b>USB15AC5</b>	<b>USB20AC5</b>
high power 5 Amp, 5 Volt USB output,	Gray	<b>USB15AC5GY</b>	<b>USB20AC5GY</b>
USB ports rated 10,000 cycles	Ivory	<b>USB15AC5I</b>	<b>USB20AC5I</b>
Commercial Grade Tamper-Resistant duplex receptacle	Light Almond	<b>USB15AC5LA</b>	<b>USB20AC5LA</b>
	White	<b>USB15AC5W</b>	<b>USB20AC5W</b>



USB15AC5W

### USB Charger Type A

Description	Color	15A 125V	20A 125V
USB Charger Outlet:	Black	<b>USB15A5BK</b>	<b>USB20A5BK</b>
two Type A port configurations,	Brown	<b>USB15A5</b>	<b>USB20A5</b>
high power 5 Amp, 5 Volt USB output,	Gray	<b>USB15A5GY</b>	<b>USB20A5GY</b>
USB ports rated 10,000 cycles	Ivory	<b>USB15A5I</b>	<b>USB20A5I</b>
Commercial Grade Tamper-Resistant duplex receptacle	Light Almond	<b>USB15A5LA</b>	<b>USB20A5LA</b>
	White	<b>USB15A5W</b>	<b>USB20A5W</b>



USB20A5W

**HUBBELL®**  
Wiring Device-Kellems

[www.hubbell-wiring.com](http://www.hubbell-wiring.com)

