

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0470541000](#)  
**Status:** **Active**  
**Overview:** [KK® Interconnect System - Molex](#)  
**Description:** [KK® 254 Housing with Polarization Rib, 4 Pin](#)

**Documents:**

[3D Model](#) [Product Specification PS-47053-001-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E29179

**General**

Product Family Crimp Housings  
 Series [47054](#)  
 Application Signal, Wire-to-Board  
 Overview [KK® Interconnect System - Molex](#)  
 Product Name [KK® 254](#)  
 UPC 822348237999

**Physical**

Circuits (maximum) 4  
 Color - Resin Ivory  
 Flammability 94V-0  
 Gender Female  
 Glow-Wire Compliant No  
 Lock to Mating Part Yes  
 Material - Resin Nylon  
 Net Weight 0.522/g  
 Number of Rows 1  
 Packaging Type Bag  
 Panel Mount No  
 Pitch - Mating Interface 2.54mm  
 Pitch - Termination Interface 2.54mm  
 Polarized to Mating Part Yes  
 Stackable No  
 Temperature Range - Operating See Product Specification

**Electrical**

Current - Maximum per Contact 4.0A


**Solder Process Data**

Duration at Max. Process Temperature (seconds) 005  
 Lead-free Process Capability N/A  
 Max. Cycles at Max. Process Temperature 001  
 Process Temperature max. C 230

**Material Info**

**Reference - Drawing Numbers**

Product Specification PS-47053-001-001  
 Sales Drawing SD-47054-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/01/2017 (12  
 January 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[47054 Series](#)

**Mates With**

[47053 2.54mm Pitch KK® Vertical Header, with Friction Lock](#)

**Use With**

[2759 KK® Crimp Terminal, 22-30 AWG](#)