


# INTERCONNECTION

## Pluggable Terminal Strips Plug in Style

- Moulded in natural PA6, self extinguishing to UL94-V2
- Printing available on request
- CE Approved

CTSN/MF



### SPECIFICATION

Voltage (max)	450V AC
Working temperature	110°C
No. of poles	2
Moulding	UL94-V2 Self extinguishing PA6
Conducting bush	Nikel plated brass
Screws	Zinc, plated steel

### MALE

TYPE NO.	SIZE / RATING	INSERT DIAMETER	TERMINAL SCREWS	LENGTH	WIDTH	HEIGHT	PITCH	FIXING HOLE DIAMETER	MAX CURRENT
CTSN434/2/M	12.5mm/16A	4.3mm	M3.5	20.1mm	23.5mm	19mm	12.3mm	3.5mm	57A

### FEMALE

TYPE NO.	SIZE / RATING	INSERT DIAMETER	TERMINAL SCREWS	LENGTH	WIDTH	HEIGHT	PITCH	FIXING HOLE DIAMETER	MAX CURRENT
CTSN434/2/F	12.5mm/16A	4.3mm	M3.5	20.1mm	23.5mm	19mm	12.3mm	3.5mm	57A

PCB  
TERMINAL  
BLOCKS

INTER-  
CONNECTION

FUSES &  
FUSE-  
HOLDERS

LEDS &  
INDICATORS

MINIATURE  
SWITCHES

LIMIT &  
SAFETY  
SWITCHES

CONTROL  
PRODUCTS

INTERFACE  
MODULES &  
SUPPORTS

RELAY  
BASES

DIN RAIL  
ENCLOSURES

BATTERIES

SOLAR  
PANELS

TRANS-  
FORMERS