

BLACK BOX NETWORK SERVICES - 1000 PARK DRIVE LAWRENCE, PA 15055

DATE: 4/4/2017

RE: PRODUCT CANCELLATIONS

The following product codes have been canceled effective immediately:

CODE	DESCRIPTION	REPLACEMENT	QO H
KVT217A-R2	17" DUAL RAIL KVM TRAY W/ TRACKBALL MOUSE, PS/2 USB	KVT417A-1UV-R3	0
ME191A	PARALLEL LINE DRIVER-R CENTRONICS MALE/TERM BLCK	None	2
ME193A	PARALLEL LINE DRIVER-R CENTRONICS MALE/RJ11	None	4
ME190A	PARALLEL LINE DRIVER-T DB25 MALE/TERM BLCK	None	5
ME192A	PARALLEL LINE DRIVER-T DB25 MALE/RJ11	None	2
EPL100	MAGNETIC FLEXIBLE NECK LIGHT	None	22
EPL115	GROUND FAULT INTERRUPTER CORD W/ CIRCUIT BREAKER	None	11
ETN62A	COAXIAL PVC CABLE BULK RG62	None	0
ETN62A-0500	BULK COAXIAL PVC CABLE RG62	None	0
ETN62A-1000	BULK COAXIAL PVC CABLE RG62	None	0
ETN62A-150M	RG62 COAX BNC CABLE 150M	None	0
ETN62AJ	BULK COAXIAL PVC CABLE RG62-JAPAN	None	0
ETN62AX	RG62 NEC TYPE CLC JAPAN	None	0
ETN62-BNC	COAX CABLE RG62 BNC	None	0
ETN62XX	RG62 BNC-BNC JAPAN	None	0
FD010	TWINAX CONN MALE	None	0
FD010-10PAK	TWINAX CONN MALE-10PAK	None	1
FA550-10PAK	TRANCIEVER CONN KIT-10 PAK	None	0
FA550	TRANCIEVER CONN KIT- MALE	None	20
FA551	TRANCIEVER CONN KIT-FEM	None	6
FA551-10PAK	TRANCIEVER CONN KIT 10PAK FEM	None	0
ETN59A-1000	BULK COAXIAL PVC CABLE RG59	None	1
ETN59A-0500	BULK COAXIAL PVC CABLE RG59	None	0
ETN59A	BULK COAXIAL PVC CABLE RG59-CUSTOM LENGTH	None	0
LCN300A-1000	THINNET CABLE BULK BLK PVC	None	0
LCN300A-0500	THINNET CABLE BULK BLK PVC	None	1
LCN300A	THINNET CABLE BULK BLK PVC-CUSTOM LENGTH	None	0
LCN300-0020-LM	THINNET CABLE BLK PVC	None	0
LCN300AJ	THINNET CABLE BLK PVC-JAPAN	None	0
LCN300AX	THINNET CABLE BLK PVC-JAPAN	None	0
LCN300J	THINNET CABLE BLK PVC-JAPAN	None	0
FT188	CATV RG59, RG6 HEX DIE SET	None	1
CIQ-FTKSFP	COPPER/FIBER TECHNICIANS KIT (CIQ-KIT + FTK1000)	None	1
FA801	TWO-HEADED HOOD-COVER ONL	None	89
990DSL	LOOP TESTER (BASE UNIT)	None	1
JR-SYS-2-H	JACKRAPID REPL BLADE HEAD	None	1
22800001	TS22 TEST SET W/ PIERCING PIN CLIPS	None	2
TPAK	METER HANGING KIT	None	4

FT200-R2	ANTI-STATIC SERVICE KIT WITH STORAGE BAGS	None	150
36901	EXTRA DEEP DEVICE BOX	None	3
36902	EXTRA DEEP DEVICE BOX	None	13
LBH100A-H-MT	MC SWITCH HARDENED 10/100 MM 100-240-VAC MTRJ	LBH100A-H-SC	2
LBH100A-H-MT-24	MC SWITCH HARDENED 10/100 MM 24-VDC MTRJ	LBH100A-H-SC-24	18
LBH100A-MT	MC SWITCH STANDARD 10/100 MM 115-VAC MTRJ	LBH100A-SC	0
LBH100A-P-MT	M C SWITCH EXTREME 10/100 MM 95-260-VAC MT	LBH100A-P-SC	0
60961-32	HL10 HANDSET LIFTER	None	0
64338-31	SUPRAPLUS WIDEBAND HW251N	None	1
64339-31	SUPRAPLUS WIDEBAND HW261N	None	2
82783-11	CALISTRO P540 COMMUNICATOR	None	0
M22	VISTA AMPLIFIER WITH CLEARLINE AUDIO	None	0
CC1600-11L	16 CARD RACK FOR MT5600BR-V92	None	0
MT5600BA-V92-NAM	V92 DIALUP2/4WLEASE MODEM DATA/FAX 100-240 US CORD	None	0
PS1600	REDUNDANT POWER SUPPLY	None	0
AC2000A	DVI-D WITH AUDIO EXTENDER W/ EDID	AVX-DVI-TP-100M	7
UCCSHELFL	LARGE SHELF POWER WRAP, 9 SLOTS, 17 IN DEEP	None	186
PSD012	30 WATTS 1.5A 24VDC OUTPUT	MDR-40-24	11
PSD014	75 WATTS 1.6A 48VDC OUTPUT	SDR-120-48	8
ACUREMSW	EXTENDER REMOTE MODULE W/ INTEGRATED KVM SWITCH	None	0
ACUR002A	REMOTE UNIT CATX EXTENDER DUAL VIDEO	None	0
ACU1049A	CAT5 KVM EXTENDER DUAL ACCESS W/BUILT-IN SWITCH	None	4
ACU1006MRVA	6-PRT CAT5 KVM EXT MICRO RMTE W/SERL & AUDIO SUPRT	None	0
ACU1006MRA	6-PORT CAT5 KVM EXTENDER MICRO REMOTE RACKMNT HUB	None	0
ACUR004A	CATX REMOTE EXTENDER FOR QUAD VIDEO	None	0
ACUVREM	BIDIRECTIONAL SERIAL AND STEREO AUDIO	None	1
ACU1006SRA	CAT5 KVM EXTENDER HUB W/ SERIAL, 6-PORT	None	2
ACURA004A	CATX REMOTE EXTENDER FOR QUAD VIDEO SERIAL N AUDIO	None	0
ACU1012RA	CAT5 KVM EXTENDER HUB 12-PORT	None	1
ACU1006VRA	6-PORT BIDIRECTIONAL SERIAL AND STEREO AUDIO	None	1
ACUSREM	CAT 5 KVM EXTENDER SERIAL REMOTE MODULE	None	10
ACU1006RA	CAT5 KVM EXTENDER HUB 6-PORT	None	11
ACU1006DVRA	6 PORT DUAL(LCAL KVM PRT) BIDIRECTIONALSERL & AUDI	None	5
ACU1006DRA	CAT5 KVM EXTENDER HUB DUAL ACCESS	None	3
ACUREM	CAT 5 KVM EXTENDER REMOTE MODULE	None	3

ACU1007A	CAT5 KEYBOARD & MOUSE EXTENDER	None	1
ACURA001A	RMT UNIT CATX KVM EXTDR WITH SERIAL AND AUDIO	None	0
ACURA002A	REMOTE UNIT CATX EXTENDER DUAL VIDEO SERIAL AUDIO	None	0
ACUMREM	CAT5 MICRO EXTENDER REMOTE UNIT	None	67
ACU1006DSRA	SERVSWITCH DUAL ACCESS SERIAL HUB SINGLE 6 PORT	None	6
ACU2201A-R2	CATX KVM EXTR KIT DUAL VIDEO SINGLE ACCESS	None	0
ACU2209A	KVM EXTENDER WITH DUAL VG A, AND ACCESS	None	7
ACU2222A-R2	CATX KVM EXTR SINGLE KIT DUAL VIDEO SERIAL AUDIO	None	13
ACU2228A	KVM EXTENDER WITH DUAL VG A, &ACCESS, SRL, AUDIO	None	4
DTX5000	KVM OVER IP EXTENDER	None	0
DTX5000-CTL-R2	DTX CONTROL APPLIANCE USE W/ DTX500X -T OR -R UNITS	None	0
DTX5001	DVI-D &/VGA KVM/IP TX & RX EXTENDER KIT	DTX1000	0
DTX5001-R	DVI-D &/VGA KVM/IP RECEIVER EXTNDER	DTX1000-R	0
DTX5001-T	DVI-D &/VGA KVM/IP TRASMITTER EXTNDER	DTX1000-T	3
DTX5001-T-RMK	RACKMOUNT KIT FOR (2) DTX5001-T		0
DTX5002	DUAL HEAD KVM OVER IP TX & RX EXTENDER KIT	DTX1002	0
DTX5002-R	DUAL HEAD KVM OVER IP RECEIVER EXTENDER	DTX1002-R	10
DTX5002-T	DUAL HEAD KVM OVER IP TRANSMITTER EXTENDER	DTX1002-T	12
DTX5000-PS-R2	DTX TRANSMITTER/RECEIVER POWER SUPPLY	None	6
DTX5000-MMK	DTX5000 RECEIVER MOUNTING PLATE	None	0
KV1700A	SERVSWITCH OCTET 4 USERS X 42 SERVERS MATRIX KVM	None	0
KV1701A	SERVSWITCH OCTET 8 USERS X 32 SERVERS MATRIX KVM	None	0
KV1702A	SERVSWITCH OCTET 16 USERS X 64 SERVERS MATRIX KVM	None	0
KV1703A	SERVSWITCH OCTET 4 USERS X 16 SERVERS MATRIX KVM	None	1
KV1711A-R2	SERVSWITCH OCTET USER STATION BASIC	None	4
KV1711E-R2	SERVSWITCH OCTET USER STATION BASIC	None	0
KV1712A-R2	SERVSWITCH OCTET USER STATION ENHANCED VIDEO	None	70
KV1720A	SERVSWITCH OCTET SAM FOR PS/2 COMPUTERS	None	72
KV1721A	SERVSWITCH OCTET SAM FOR USB COMPUTERS	None	50
KV1725A	SERVSWITCH OCTET DUAL SAM FOR PS/2 + AUDIO & SERIAL	None	21
KV1726A	SERVSWITCH OCTET DUAL SAM FOR USB + AUDIO & SERIAL	None	5

KV1727A	SERVSWITCH OCTET DUAL SAM FOR SUN + AUDIO & SERIAL	None	5
RMK171X	1U RACKMOUNT KIT FOR KV17 10A AND KV1712A	None	0
KVT8CATUV	VGA & 8 CATX PORTS USE W/KVT41X, KVT51X TRAY	None	2
KVT417A-8CATX	17IN 1U LCD TRAY 1 VGA, 8 PORT CATX SWITC	None	0
KVT419A-8CATX	19IN 1U LCD TRAY 1 VGA, 8 PORT CATX SWITCH	None	0
KVT517A-8CATX	17IN 1U LCD TRAY 1 VGA, 8 PORT CATX SWITCH	None	0
KVT1IP8CATUV	VGA & 8CATX W (1) IP POR USE W/KVT41X, KVT51X TRAY	None	1
KVT417A-8CATX-1IP	17IN 1U LCD TRAY 1 VGA, 8 PORT CATX W(/1)	None	0
KVT419A-8CATX-1IP	19IN 1U LCD TRAY 1 VGA, 8 PORT CATX W(/1)	None	0
KVT517A-8CATX-1IP	17IN 1U LCD TRAY 1 VGA, 8 PORT CATX W(/1)	None	0
ACR2004A	SERVSWITCH WIZARD IP	None	4
AVU5010A	WIZARD MULTIMEDIA KIT W/ STEREO AUDIO	None	27
AVU5011A	WIZARD MULTIMEDIA REC W/STEREO AUDIO	None	40
AVU6010A	WIZARD M/MEDIA + AV/RS232 TX/RX	None	21
JHOOK-32-E-100	J HOOK, 2", SIZE 32 END HOOK, 100	None	37
JHOOK-32-A-C-100	J HOOK, 2", SIZE 32 90 DEGREE ANGLE CCP, 100	None	16
JHOOK-32-A-100	J HOOK, 2", SIZE 32 90 DEGREE ANGLE, 100	None	0
JHOOK-32-B-C-100	J HOOK, 2", SIZE 32 BATWING CCP, 100	None	0
JHOOK-32-S-C-100	J HOOK, 2", SIZE 32 STANDARD CCP, 100	None	5
JHOOK-64-S-25	J HOOK, 4", SIZE 64 STANDARD, 25	None	0
RM097	ADJUSTABLE SHELF FOR RM096A	None	0
RM098	HINGED PANEL 19" FOR RM096A	None	7
RM099	HINGED DUST COVER FOR RM096A	None	21
PRP1000A	POWER REBOOT POD SINGLE PORT PWR CNTRL DEV	None	3
SSKX0002266	REPLACEMENT MULTICABLE FOR ACU5110A AND ACU5114A	None	8
TSCAB30U-A-H	HARDWARE FOR TSCAB30U-A	None	20
PS102E	230V P/S - DT100, DT200	None	1
RMT924	ACTION ORGANIZER 6" D RING CABLE MGMT KIT	None	10
ECAIRFLOW42	ELITE AIR FUNNEL KIT 42" DEEP	None	1
TPTS345379	EPXR14 3FT	None	2
EC72012436T	EC38U 72X24X36 FRAME TAP PAILS PDU MTS LGS	None	3
TOCG365971	FILTER KIT FOR BLACK BOX RM386 FAN	None	1
TOCG394950	SP216A-R2 MOUNTING HARDWA RE	None	10
TORK0002015	VELCRO PLENUM RATED CRANBERRY 3/4" X 75FT	None	6
LICENSEKEY	INTELLI-PASS LICENSE KEY FOR MGMT SFTW SAC500MSA-	NONE	0

SAC500MSA-5-R2	INTELLI-PASS MGMT, ENROLL SFTWR,SCANNER;TO 5 DOORS	NONE	0
SAC506SCA	ENROLLMENT SCANNER, USB, FOR INTELLI- PASS	NONE	0
SAC510NA	INTELLI-PASS BIOMETRIC ACCESS CONTROL - NTWKD	NONE	0
SAC530NA	INTELLIPASS TRIAD BIOMETRIC ACCESS CONTROL	NONE	0
LMC1007A-R3	FLEXPOINT GX, GIGABIT MEDIA CONVERTER 1000BASET	LMC1003A-R3	0
LMC100A-RJ-R3	FLEXPOINT 10/100BASETX CONVRTS 10/100BASETX RJ45	LMC100A-SC-R3	0
LMC1002A	FLEXPT 1000FF, CONVERTS 1000BASE-X FIBER, SX/MM/	LMC1003A-R3	0
LMC200A-2PS-DC	FLEXPOINT POWERED CHASSIS 2 POWER SUPPLIES 48VDC	LMC200A-2PS-DC	1
LMC212A-SM-SLH	FLEXPOINT 10FL/T CONVERT 10BASET RJ45 TO 10BASEFL	LMC212A-SM-R3	0
LMC213A-MMRJ	FLEXPOINT 100FX/TX CONVRT 100BASETX RJ45 TO 100BASE	LMC213A-MMSC-R2	0
LMC214A-SCP-R2	FLEXPOINT 100TX/FX CONVRT PLUS(UP TO 56KM)(SM/SC)	LMC213A-SMST-R2	0
LES301AE-KIT	1-PORT 10/100 DEV SERV RS232/422/485 DB9M W PWR	LES301A	0
PI125A	SERIAL TO PARALLEL CONVERTER NON- PWRED	PI125A-R2	0
FRA120-S05-4	DESKTOP STYLE POWER SUPPLY	NONE	0
RM718	LARGE CLAMP WASHER 50PAK	NONE	0
RM719	SMALL CLAMP WASHER 50PK	NONE	4
KV1713A	SERVSWITCH OCTET USER STATION MULTIMEDIA	NONE	-5
LMC5103A-R2	1 SLOT DESKTOP CHASSIS MULTI PWR AC / DC	LMC5201A	8
LMC5233A	3 SLOT CHASSIS 1 AC DESKTOP	LMC5201A	5
LMC5234A	3 SLOT CHASSIS 2 AC DESKTOP	LMC5201A	5
LMC5238A	RACK MT SHELF FOR DESKTOP/MULTI/COMPACT/	NONE	0
LMC5124C-R3	L2 TX/SSFX SM-SC (1310XMT 1550RCV) W/ LFPT	NONE	8
EFN12-36	12 FIBER BUFFER TUBE FAN OUT KIT 36 IN	NONE	23
FO032	PREPOLISHED FIBER CONNECTOR SC	NONE	780
FT538	FIBER OPTIC CLEAVER	NONE	1
VCH-HDMI-010M	HYBRID HIGH SPEED HDMI CABLE	NONE	1
VCH-HDMI-015M	HYBRID HIGH SPEED HDMI CABLE	NONE	0

VCH-HDMI-020M	HYBRID HIGH SPEED HDMI CABLE	NONE	0
VCH-HDMI-025M	HYBRID HIGH SPEED HDMI CABLE	NONE	0
VCH-HDMI-030M	HYBRID HIGH SPEED HDMI CABLE	NONE	0
VCH-HDMI-035M	HYBRID HIGH SPEED HDMI CABLE	NONE	0
VCH-HDMI-040M	HYBRID HIGH SPEED HDMI CABLE	NONE	0
VCH-HDMI-045M	HYBRID HIGH SPEED HDMI CABLE	NONE	0
VCH-HDMI-050M	HYBRID HIGH SPEED HDMI CABLE	NONE	1
VCH-HDMI-060M	HYBRID HIGH SPEED HDMI CABLE	NONE	0
VCH-HDMI-070M	HYBRID HIGH SPEED HDMI CABLE	NONE	0
VCH-HDMI-080M	HYBRID HIGH SPEED HDMI CABLE	NONE	0
VCH-HDMI-090M	HYBRID HIGH SPEED HDMI CABLE	NONE	0
FT099A-R2	MODULAR PLUG CRIMP TOOL KIT	NONE	1
FAB422	RJ45 FEMALE TO DB25 FEMALE BULK SHIELDED TWISTED PAIR 24 CONDUCTOR	CBCC296650	0
ESN24A	BULK SHIELDED TWISTED PAIR 24 CONDUCTOR	NONE	0
ESN24A-0500	BULK SHIELDED TWISTED PAIR 24 CONDUCTOR	NONE	0
ESN24A-1000	BULK SHIELDED TWISTED PAIR 24 CONDUCTOR	NONE	0
TS140-R2	THREE FUNC. MODULAR TEST	NONE	10
FM342	ST snap fitting	NONE	19
WP283-R4	2 Port Surface Mount Housing	NONE	130
WP378-R4	2 Port Surface Mount Housing	NONE	135
WP461	GIGA STATION WALL PLATE	NONE	123
WP468	GIGA STATION WALL PLATE	NONE	100
WP480	GIGA STATION WALL PLATE	NONE	74

Thank You

Becky Pihou
Customer Sales & Service
Black Box Corporation
Office: 724-873-6368
becky.pihou@BlackBox.com

