

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0191990008**  
**Status:** **Active**  
**Overview:** Splices  
**Description:** Avikrimp™ Window Butt Connector for 18-22 AWG Wire, Mylar Tape Carrier

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-015-001 \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family Splices  
 Series 19199  
 Comments Mil Spec M7928/5-3  
 Crimp Quality Equipment Yes  
 Mil-Spec M7928/5-3  
 Overview Splices  
 Product Name Avikrimp™, Butt - Window  
 UPC 800753046818

**Physical**

Barrel Type Closed  
 Color - Resin Red  
 Insulation Nylon (PA)  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 1.194/g  
 Packaging Type Adhesive Tape on Reel  
 Temperature Range - Operating -55°C to +105°C  
 Wire Insulation Diameter 3.56mm max.  
 Wire Size AWG 18, 20, 22  
 Wire Size mm² 0.25-1.50

**Electrical**


Voltage - Maximum 300V

**Material Info**

Engineering Number WA-840T

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-015-001  
 Sales Drawing SD-19199-003



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/01/2017 (12  
 January 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

19199 Series