

Basic

Brand Name:	Acer
DVI:	Yes
Environmentally Friendly:	Yes
Graphics Controller	Intel
Manufacturer:	
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
Number of USB 2.0 Ports:	4
Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro
Optical Drive Type:	DVD-Writer
Processor Manufacturer:	Intel
Processor Model:	i3-6100
Processor Speed:	3.70 GHz
Processor Type:	Core i3
Product Family:	Extensa M2710
Product Type:	Desktop Computer
Standard Memory:	4 GB
Total Hard Drive Capacity:	1 TB
Total Number of USB Ports:	6
VGA:	Yes

Display & Graphics

Graphics Controller	Intel
Manufacturer:	
Graphics Controller Model:	HD Graphics 530
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
TV Card:	No

General Information

Brand Name:	Acer
Manufacturer Part Number:	DT.X0TEK.005
Manufacturer Website Address:	http://www.acer.co.uk
Manufacturer:	Acer, Inc
Product Line:	Extensa
Product Name:	Extensa M2710 Desktop Computer
Product Series:	M2710
Product Type:	Desktop Computer

I/O Expansions

Number of M.2 Interfaces:	1
Number of PCI Express x1	1
Slots:	
Number of PCI Express x16	1
Slots:	
Number of Total Expansion	2
Slots:	

Input Devices

Keyboard Type:	Physical Keyboard
Keyboard:	Yes
Pointing Device Type:	Mouse

Interfaces/Ports

Audio Line In:	Yes
Audio Line Out:	Yes
DVI:	Yes
Modem (RJ-11):	No
Network (RJ-45):	Yes
Number of USB 2.0 Ports:	4
Number of USB 3.1 Gen 1 Ports:	2
Total Number of USB Ports:	6
VGA:	Yes

Memory

Maximum Memory:	16 GB
Memory Card Reader:	No
Memory Standard:	DDR4-2133/PC4-17000
Memory Technology:	DDR4 SDRAM
Standard Memory:	4 GB

Miscellaneous

Certifications & Standards:	<ul style="list-style-type: none">• DMI• PC2001• BSMI• CB• CE• FCC
Environmental Certification:	RoHS
Environmentally Friendly:	Yes
Features:	Security Slot
Package Contents:	<ul style="list-style-type: none">• Extensa M2710 Desktop Computer• USB Keyboard• USB Mouse

Network & Communication

Ethernet Technology:	Gigabit Ethernet
Modem:	No

Physical Characteristics

Depth:	372 mm
Height:	365 mm
Width:	175 mm

Power Description

Maximum Power Supply Wattage:	220 W
-------------------------------	-------

Processor & Chipset

64-bit Processing:	Yes
Cache:	3 MB
Chipset Manufacturer:	Intel
Chipset Model:	H110 Express
Direct Media Interface:	8 GT/s
Hyper-Threading:	Yes
Number of Processors Installed:	1
Number of Processors Supported:	1
Processor Core:	Dual-core (2 Core)
Processor Manufacturer:	Intel
Processor Model:	i3-6100
Processor Speed:	3.70 GHz
Processor Type:	Core i3
vPro Technology:	No

Software

Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro

Storage

Hard Drive Configuration:	1 x 1 TB
Hard Drive Interface:	Serial ATA/300
Hard Drive RPM:	7200
Number of Hard Drives:	1
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Total Hard Drive Capacity:	1 TB